



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C25BNF240A Compact 2P 40A Cont Box Lug Term Quad QC 120VAC CO

Eaton Corp

Catalog Number	C25BNF240A
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Quick, 30A, 24 Vac, 50/60 HZ, Open With Metal Mounting Plate, Compact, Two-Pole, 30A, Contactor, Two-Pole, 40A, Box Lugs (Posidrive Setscrew) and Quick Connect Terminals (Side-By-Side), Non-Reversing
Weight per unit	0.6000 (lbs/each)
Product Category	Definite Purpose Contactors

Features

Enclosure Type	Open with metal mounting plate
----------------	--------------------------------

Dimensions and Weight

Depth	2.32
Height	3.19
Width	1.97

Descriptions

Description	COMPACT 2P 40A CONT BOX LUG TERM QUAD QC 120VAC CO
extra long description	ETN C25BNF240A COMPCT 2P 40A CONT B
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Quick, 30A, 24 Vac, 50/60 Hz, Open with metal mounting plate, Compact, two-pole, 30A, Contactor, Two-pole, 40A, Box lugs (posidrive setscrew) and quick connect terminals (side-by-side), Non-reversing
Product Type	Compct 2P 40A Cont Bxlug TRM 4QC 120ac

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685116150
Manufacturers Part Number	C25BNF240A
UPC	786685116150

Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor

Packaging

Carton	1
Weight Per each	0.6



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

standard

CSA Certified,UL Recognized,RoHS Compliant