



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **C25DND230B Open N-R 2P 30A DP Cont SCR/PP W/QC Term 240VAC CO** *Eaton Corp*

Catalog Number	C25DND230B
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Quick, 30A, 208-240 Vac At 50/60 HZ, Open With Metal Mounting Plate, 15-50A, Two- or Three-POLE30A, Contactor, Two-Pole, Global Ratings, Screw/Pressure Plate and Quick Connect Terminals (Side-By-Side)
Weight per unit	1.2 (lbs/each)
Product Category	Definite Purpose Contactors

### **Features**

connection	Quick
dimensions	3.3500 IN X 2.4000 IN X 3.7500 IN
Enclosure Type	Open with metal mounting plate

### **Descriptions**

Description	OPEN N-R 2P 30A DP CONT SCR/PP W/QC TERM 240VAC CO
extra long description	ETN C25DND230B OP N-R 2P 30ADPCNT S
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Quick, 30A, 208-240 Vac at 50/60 Hz, Open with metal mounting plate, 15-50A, two- or three-pole30A, Contactor, Two-pole, Global ratings, Screw/pressure plate and quick connect terminals (side-by-side)
Product Type	Op N-R 2P 30ADPCNT SCR/PP W/Qc240ac

### **Manufacturer Information**

Brand	EATON CUTLER-HAMMER
GTIN	00782116300365
Manufacturers Part Number	C25DND230B
UPC	782116300365

### **Taxonomies, Classifications, and Categories**

Category Description	DP CONTACTORS
Type	Definite purpose contactor

### **Packaging**

Carton	1
Weight Per each	1.19



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels  
and OEMs

standard

CSA Certified,UL Recognized,RoHS Compliant