ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



# C30 3/0 Cu Long Barrel Compression Butt Splice

*Nsi Industries*

| | |
|---|---|
| Catalog Number | C30 |
| Manufacturer | Nsi Industries |
| Description | Long Barrel Tinnedcoppersplice 3/0 Awg Long Barrel Tinned Coppersplices Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed. |
| Weight per unit | 0.1500 (lbs/each) |
| Product Category | Large Terminals & Connectors |

## Features

| | |
|---|---|
| Material | Copper |
| Number of Conductors | 2 |
| Poles | 1 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |

## Material, Color, and Finish

| | |
|---|---|
| Color | Orange |
| Finish | Tin Plated |

## Dimensions and Weight

| | |
|---|---|
| Size | L=2.25 - OD=.620 - ID=.490 |

## Descriptions

| | |
|---|---|
| Description | 3/0 CU LONG BARREL COMPRESSION BUTT SPLICE |
| extra long description | NSI C-3/0 Tinned Copper Splice- Lon |
| Features | Long Barrel Tinned Copper Splice 3/0 AWG: Long Barrel Tinned Copper Splices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed. |
| Long Description | Long Barrel TinnedCopperSplice 3/0 AWG Long Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed. |
| Product Type | Tinned Copper Splice- Long Barrel, 3/0 Awg |
| Special Features | 3/0 AWG (STR) - CU Splice |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Manufacturer Information

| | |
|---|---|
| Brand | Nsi Industries |
| GTIN | 00662381037572 |
| Manufacturers Part Number | C-3/0 |
| UPC | 662381037572 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Long Barrel - CU Splice |

## Packaging

| | |
|---|---|
| Carton | 1 |
| Package | 25 |
| Weight Per each | 0.15 |

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | Terminate, Splice, Tap Power Connectors |
| environmental conditions | 90 C |
| standard | UL486A/B, UL467 (8 AWG -3/0 AWG) |
| Temperature Rating | 90 C |