



Powering Business Worldwide

pe.eaton.com

NEMA Freedom Thermal Overload Relay

C306DN3B

UPC:782113973234

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes: Series B overload relays have load lugs built into relay base and will only accept Series B heater packs. These relays can be directly attached to a contactor or they can be DIN rail or panel mounted using an adapter.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 20-39A
- **Design:** NEMA, IEC
- **Frame Size:** NEMA Size 00, 0, IEC Size A-F
- **Mounting:** DIN rail, panel
- **Number Of Poles:** Three-pole
- **Special Features:** Heaters required
- **Trip Type:** Thermal
- **Used With:** GST00-160

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Motor Starters and Contactors - Low Voltage Catalog](#)
- [C306DN3B 3D Inventor](#)
- [C306DN3B 2D PDF](#)
- [C306DN3B 2D Drawing Xchange](#)
- [C306DN3B AutoCAD 2D Footprint \(mm\)](#)



- [C306DN3B AutoCAD 2D Footprint](#)
- [C306DN3B 3D Model Xchange](#)
- [Eaton Specification Sheet - C306DN3B](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

pe.eaton.com

NEMA Freedom Thermal Overload Relay

C306DN3B

UPC:782113973234

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes: Series B overload relays have load lugs built into relay base and will only accept Series B heater packs. These relays can be directly attached to a contactor or they can be DIN rail or panel mounted using an adapter.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 20-39A
- **Design:** NEMA, IEC
- **Frame Size:** NEMA Size 00, 0, IEC Size A-F
- **Mounting:** DIN rail, panel
- **Number Of Poles:** Three-pole
- **Special Features:** Heaters required
- **Trip Type:** Thermal
- **Used With:** GST00-160

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Motor Starters and Contactors - Low Voltage Catalog](#)
- [C306DN3B 3D Inventor](#)
- [C306DN3B 2D PDF](#)
- [C306DN3B 2D Drawing Xchange](#)
- [C306DN3B AutoCAD 2D Footprint \(mm\)](#)



- [C306DN3B AutoCAD 2D Footprint](#)
- [C306DN3B 3D Model Xchange](#)
- [Eaton Specification Sheet - C306DN3B](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data

© 2016 Eaton. All rights reserved.