



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C25DNF325T Open N-R 3P 25A DP Cont Box Lugs W/QC Term 24VAC C

Eaton Corp

Catalog Number	C25DNF325T
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Mounting Plate, Quick, Quick Connect , 12 Vac, 50/60 HZ, Open With Metal Mounting Plate, 15-50A, Two- and 3P, 25A, Contactor, 3P, Global Listed, D1, Box Lugs (Posidrive Setscrew), Non-Reversing
Weight per unit	1.2 (lbs/each)
Product Category	Definite Purpose Contactors

### Features

Coil Voltage	120 Vdc
connection	Quick
dimensions	3.3500 IN X 2.4000 IN X 3.7500 IN
Enclosure Type	Open with metal mounting plate

### Descriptions

Description	OPEN N-R 3P 25A DP CONT BOX LUGS W/QC TERM 24VAC C
extra long description	ETN C25DNF325T OP N-R 3P 25ADPCNT B
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Mounting plate, Quick, Quick connect , 12 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and 3P, 25A, Contactor, 3P, Global listed, D1, Box lugs (posidrive setscrew), Non-reversing
Product Type	Op N-R 3P 25ADPCNT BXLGS W/Qc24ac

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116300570
Manufacturers Part Number	C25DNF325T
UPC	782116300570

### Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor

### Packaging

Carton	1
Weight Per each	1.19



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels  
and OEMs

standard

UL Recognized, CSA Certified, UL Listed file E1491 (Guide Number  
NLDX2), RoHS Compliant