ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C2WH6 2" Wiring Duct Cover, White

Panduit Corporation

Catalog Number	C2WH6
Manufacturer	Panduit Corporation
Description	The C2WH6 PVC Flush Wiring Duct Cover Features A Non-Slip, Liner to Prevent Cover Slide. Designed With The User In Mind, The Cover Is Easy to Install and Remove. The General-Purpose Lead-Free PVC Material Is Suitable For Use In Indoor Applications. Ul 94 Flame Class Of V-0 With A Ul Recognized Continuous-Use Temperature Up to 122°F (50°C). 0.35" X 2.25" (8.9 MM X 57.2 MM) and 6' (1.83 M) Long. Color White.
Weight per unit	0.1220 (lbs/each)
Product Category	Wiring Duct & Accessories

Features

connection	Snap-on
media	Yes

Material, Color, and Finish

Color	White

Dimensions and Weight

Length	NA
Width	2.25

Descriptions

Description	2" WIRING DUCT COVER, WHITE
extra long description	PAN C2WH6 Panduct® C2WH6 Flush Duct
Long Description	The C2WH6 PVC Flush Wiring Duct Cover features a non-slip, liner to prevent cover slide. Designed with the user in mind, the cover is easy to install and remove. The general-purpose lead-free PVC material is suitable for use in indoor applications. UL 94 flame class of V-0 with a UL recognized continuous-use temperature up to 122°F (50°C). 0.35" x 2.25" (8.9 mm x 57.2 mm) and 6' (1.83 m) long. Color White.
Product Type	Panduct® C2WH6 Flush Duct Cover

Manufacturer Information

Brand	PANDUIT
GTIN	00074983230822
Manufacturers Part Number	C2WH6
UPC	074983230822

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	WIRE DUCT AND COVERS
Type	Flushed Duct Cover

Availability

minimum qty	6

Packaging

Carton	120
Weight Per foot	0.122

Uses, Certifications, and Standards

Application	Cover for Wiring Duct
standard	CE Compliant;CSA Certified;Flammability Ratings: UL94 V-0;RoHS Compliant;UL Recognized