



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C500 500 Cu Long Barrel Compression Butt Splice

Nsi Industries

| | |
|------------------|--|
| Catalog Number | C500 |
| Manufacturer | Nsi Industries |
| Description | Long Barrel TINNEDCOPPERSPLICE500 MCM Long Barrel Tinned Coppersplices Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed. |
| Weight per unit | 0.5700 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|----------------------|--------|
| Material | Copper |
| Number of Conductors | 2 |
| Poles | 1 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |

Material, Color, and Finish

| | |
|--------|------------|
| Color | Brown |
| Finish | Tin Plated |

Dimensions and Weight

| | |
|------|----------------------------|
| Size | L=4.25 - OD=1.06 - ID=.830 |
|------|----------------------------|

Descriptions

| | |
|------------------------|--|
| Description | 500 CU LONG BARREL COMPRESSION BUTT SPLICE |
| extra long description | NSI C-500 CU CMP Splice Long 2/0 AW |
| Features | Long Barrel TinnedCopperSplice500 MCM Long Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed. |
| Long Description | Long Barrel TinnedCopperSplice500 MCM Long Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed. |
| Product Type | Cu CMP Splice Long 2/0 Awg |
| Special Features | 500 MCM (STR) - CU Splice |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381037633 |
| Manufacturers Part Number | C-500 |
| UPC | 662381037633 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Long Barrel - CU Splice |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 0.57 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Terminate, Splice, Tap Power Connectors |
| environmental conditions | 90 C |
| standard | UL486A/B |
| Temperature Rating | 90 C |