

Specifications

Eaton C67 SA

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, C shape, 2"



Photo is representative



General specifications

| | |
|---------------------------------|---|
| PRODUCT NAME | Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body |
| CATALOG NUMBER | C67 SA |
| UPC | 782274746234 |
| PRODUCT LENGTH/DEPTH | 9.19 in |
| PRODUCT HEIGHT | 3.13 in |
| PRODUCT WIDTH | 3 in |
| PRODUCT WEIGHT | 1.85 lb |



Powering Business Worldwide

Certifications and compliances

| | |
|----------------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE | NEC/CEC |
| NEMA RATING | 12 |

Product specifications

| | |
|-------------------|----------------------|
| SHAPE | C |
| TRADE SIZE | 2" |
| MATERIAL | Copper-free aluminum |

Resources

| | |
|--------------------------------------|--|
| CATALOGS | Crouse-Hinds series Form 7 catalog page |
| CERTIFICATION REPORTS | Condulet Form 7 Conduit Outlet Bodies and Covers UL certification Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification |
| INSTALLATION INSTRUCTIONS | IF 964 - Conduit Body Wire Pulling IF 863 - Conduit Body Wire Pulling |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - C67 SA Condulet Form 7 Industrial Grade Conduit Bodies |
| TECHNICAL SERVICE BULLETINS | Industrial Fittings Bend Radius and Cubic Capacity Chart Industrial Fittings Wire Fill Chart |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications

Eaton C67 SA

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, C shape, 2"



Photo is representative



General specifications

| | |
|---------------------------------|---|
| PRODUCT NAME | Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body |
| CATALOG NUMBER | C67 SA |
| UPC | 782274746234 |
| PRODUCT LENGTH/DEPTH | 9.19 in |
| PRODUCT HEIGHT | 3.13 in |
| PRODUCT WIDTH | 3 in |
| PRODUCT WEIGHT | 1.85 lb |



Powering Business Worldwide

Certifications and compliances

| | |
|----------------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE | NEC/CEC |
| NEMA RATING | 12 |

Product specifications

| | |
|-------------------|----------------------|
| SHAPE | C |
| TRADE SIZE | 2" |
| MATERIAL | Copper-free aluminum |

Resources

| | |
|--------------------------------------|--|
| CATALOGS | Crouse-Hinds series Form 7 catalog page |
| CERTIFICATION REPORTS | Condulet Form 7 Conduit Outlet Bodies and Covers UL certification Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification |
| INSTALLATION INSTRUCTIONS | IF 964 - Conduit Body Wire Pulling IF 863 - Conduit Body Wire Pulling |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - C67 SA Condulet Form 7 Industrial Grade Conduit Bodies |
| TECHNICAL SERVICE BULLETINS | Industrial Fittings Bend Radius and Cubic Capacity Chart Industrial Fittings Wire Fill Chart |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

