

Specifications

Eaton CCP1044CD RS

Eaton Crouse-Hinds series PowerMate CCP plug, 100A, 0.875-1.906", Four-wire, four-pole, Style 1, Copper-free aluminum, Reverse service, 600 Vac/250 Vdc



Photo is representative

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton Crouse-Hinds series PowerMate CCP plug |
| CATALOG NUMBER | CCP1044CD RS |
| UPC | 662276276680 |
| PRODUCT LENGTH/DEPTH | 10.8 in |
| PRODUCT HEIGHT | 4.13 in |
| PRODUCT WIDTH | 4.13 in |
| PRODUCT WEIGHT | 2.2 lb |



Certifications and compliances

| | |
|----------------------------|------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous |
|----------------------------|------------------------|

Product specifications

| | |
|------------------------|------|
| AMPERAGE RATING | 100A |
|------------------------|------|

| | |
|-----------------------|-----------|
| | Locations |
| STANDARDS TYPE | NEC/CEC |
| NEMA RATING | 4X |

| | |
|-------------------------|----------------------|
| GROUNDING TYPE | Style 1 |
| CONFIGURATION | Four-wire, four-pole |
| CABLE DIAMETER | 0.875-1.906" |
| VOLTAGE RATING | 600 Vac/250 Vdc |
| MATERIAL | Copper-free aluminum |
| SPECIAL FEATURES | Reverse service |

Resources

BROCHURES

[PowerMate Drilling Pin and Sleeve Devices brochure](#)

CATALOGS

[PowerMate Drilling Pin and Sleeve Devices catalog page](#)

CERTIFICATION REPORTS

[PowerMate Drilling Pin and Sleeve Devices UL certification \(Plugs and Connectors\)](#)

[PowerMate Drilling Pin and Sleeve Devices cUL certification \(Plugs and Connectors\)](#)

INSTALLATION INSTRUCTIONS

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

SPECIFICATIONS AND DATASHEETS

[PowerMate Connectors](#)

[Eaton Specification Sheet - CCP1044CD RS](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

