

Specifications

Photo is representative

Eaton CCP20034E

Eaton Crouse-Hinds series PowerMate CCP plug, 200A, 1.875-2.500", Three-wire, four-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton Crouse-Hinds series PowerMate CCP plug |
| CATALOG NUMBER | CCP20034E |
| UPC | 662276364868 |
| PRODUCT LENGTH/DEPTH | 13.25 in |
| PRODUCT HEIGHT | 7.5 in |
| PRODUCT WIDTH | 7.5 in |
| PRODUCT WEIGHT | 12.5 lb |



Certifications and compliances

| | |
|----------------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE | NEC/CEC |
| NEMA RATING | 4X |

Product specifications

| | |
|------------------------|-----------------------|
| AMPERAGE RATING | 200A |
| GROUNDING TYPE | Style 2 |
| CONFIGURATION | Three-wire, four-pole |
| CABLE DIAMETER | 1.875-2.500" |
| VOLTAGE RATING | 600 Vac/250 Vdc |
| MATERIAL | Copper-free aluminum |

Resources

| | |
|-------------------------------|---|
| 3D CAD DRAWING PACKAGE | Eaton Crouse-Hinds CCP20034E 3D drawing |
|-------------------------------|---|

| | |
|--------------------------------------|--|
| BROCHURES | PowerMate Drilling Pin and Sleeve Devices brochure |
| CATALOGS | PowerMate Drilling Pin and Sleeve Devices catalog page |
| CERTIFICATION REPORTS | PowerMate Drilling Pin and Sleeve Devices UL certification (Plugs and Connectors) |
| | PowerMate Drilling Pin and Sleeve Devices cUL certification (Plugs and Connectors) |
| INSTALLATION INSTRUCTIONS | IF 1652 - 200A PowerMate Pin and Sleeve Devices |
| SPECIFICATIONS AND DATASHEETS | PowerMate Connectors |
| | Eaton Specification Sheet - CCP20034E |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

