

Specifications



Photo is representative

Eaton CCP2-1-100CF

Eaton Bussmann series CCP UL98 fusible disconnect, 100A, UL98 fusible disconnect, Single-pole, 60 Hz, CUBEFuse, 200

General specifications

PRODUCT NAME	Eaton Bussmann series CCP UL98 fusible disconnect
CATALOG NUMBER	CCP2-1-100CF
UPC	051712709309
PRODUCT LENGTH/DEPTH	5.8 in
PRODUCT HEIGHT	3.6 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	0.52 lb
WARRANTY	Not Applicable
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL 98



Electrical rating

AMPERAGE RATING	100A
------------------------	------

Physical details

FUSE TYPE	CUBEFuse
------------------	----------

FREQUENCY RATING	50/60 Hz
SHORT-CIRCUIT RATING	200 kA
VOLTAGE RATING	347 Vac, 125 Vdc

NUMBER OF POLES	Single-pole
------------------------	-------------

General information

SPECIAL FEATURES	Finger Safe, 1/4" LOTO
-------------------------	------------------------

Resources

CATALOGS	Bussmann series complete full line catalog no. 1007 CCP2-1-100CF~1 Pole Comp Ckt Protect 100A
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CCP2-1-100CF

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications



Photo is representative

Eaton CCP2-1-100CF

Eaton Bussmann series CCP UL98 fusible disconnect, 100A, UL98 fusible disconnect, Single-pole, 60 Hz, CUBEFuse, 200

General specifications

PRODUCT NAME	Eaton Bussmann series CCP UL98 fusible disconnect
CATALOG NUMBER	CCP2-1-100CF
UPC	051712709309
PRODUCT LENGTH/DEPTH	5.8 in
PRODUCT HEIGHT	3.6 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	0.52 lb
WARRANTY	Not Applicable
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL 98



Electrical rating

AMPERAGE RATING	100A
------------------------	------

Physical details

FUSE TYPE	CUBEFuse
------------------	----------

FREQUENCY RATING	50/60 Hz
SHORT-CIRCUIT RATING	200 kA
VOLTAGE RATING	347 Vac, 125 Vdc

NUMBER OF POLES	Single-pole
------------------------	-------------

General information

SPECIAL FEATURES	Finger Safe, 1/4" LOTO
-------------------------	------------------------

Resources

CATALOGS	Bussmann series complete full line catalog no. 1007 CCP2-1-100CF~1 Pole Comp Ckt Protect 100A
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CCP2-1-100CF

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

