



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CCAXL3RW White Led Exit Combo Unv

XXX-Daybright By Signify

Catalog Number	CCAXL3RW
Manufacturer	XXX-Daybright By Signify
Description	Exit Sign and Emergency Light Fixture, 12-5/8 Inch W X 3 Inch D X 13-3/4 Inch H Size; White Finish; Abs Thermoplastic Enclosure Material; UL 924, Etl (Canada and Us) Approval; Damp Location, Commercial Application; Wall/Ceiling Mounting; 6 W Lamp Wattage
Weight per unit	N/A
Product Category	Exit Signs

Features

AC Voltage Rating	120/277 V
Battery Type	Lead Acid
DC Voltage Rating	6 V
Emergency Lamp Type	MR16 HALOGEN
Exit Lamp Type	LED
Face Type	Stencil with Extra Faceplate
Head Style	Round, Semi Recessed
Lamp Wattage	6 W
Number of Faces	Universal
Number of Lamp Heads	2

Material, Color, and Finish

Background/Plate Color	WHITE
Enclosure Material	ABS THERMOPLASTIC
Finish	white
Letter Color	RED

Dimensions and Weight

Size	12-5/8 INCH W X 3 INCH D X 13-3/4 INCH H
------	--

Descriptions

Additional Information	Temperature Rating 65 to 85 Deg F
Commodity Description	EXIT SIGNS
Description	WHITE LED EXIT COMBO UNV
Long Description	EXIT SIGN AND EMERGENCY LIGHT FIXTURE, 12-5/8 INCH W X 3 INCH D X 13-3/4 INCH H SIZE; WHITE FINISH; ABS THERMOPLASTIC ENCLOSURE MATERIAL; UL 924, ETL (CANADA AND US) APPROVAL; DAMP LOCATION, COMMERCIAL APPLICATION; WALL/CEILING MOUNTING; 6 W LAMP WATTAGE
Product Type	Exit Sign and Emergency Light Fixture



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	mcPhilben
Manufacturers Part Number	CCAXL3RW
Model	CCAX

Taxonomies, Classifications, and Categories

Category Description	Emergency & Exit Lighting
----------------------	---------------------------

Packaging

Carton	1
Weight Per each	0

Uses, Certifications, and Standards

Application	Damp Location, Commercial
Approval	UL 924, ETL (Canada and US)
Mounting	Wall/Ceiling