



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CFB4G30RCR Rec CFB, 4 Gang, 3 In, Round Cover, CR *Hubbell Wiring Devices*

Catalog Number	CFB4G30RCR
Manufacturer	Hubbell Wiring Devices
Description	Concrete Floorboxes, Galvanized Stamped Steel Box, Recessed, 4-Gang CFB Series Box For Round Covers, 3.75" Minimum Depth Of Pour, Corrosion Resistant Paint
Weight per unit	12.3 (lbs/each)
Product Category	Floor Boxes & Accessories

Features

Cable Entry	Through Cover
Knockouts	4) 3/4" - 1 1/4", 4) 1/2" - 1"
Material	Pre-Galvanized Steel

Material, Color, and Finish

Color	Metallic/Green Epoxy Paint
-------	----------------------------

Dimensions and Weight

Height	3.75
Length	11.2
Size	11.2 in x 12.09 in x 3.75 in
Width	12.09

Descriptions

Construction	Fabricated
Description	REC CFB, 4 GANG, 3 IN, ROUND COVER, CR
extra long description	HWDK CFB4G30RCR REC CFB, 4 GANG, 3
Long Description	Concrete Floorboxes, Galvanized Stamped Steel Box, Recessed, 4-Gang CFB Series Box for Round Covers, 3.75" Minimum Depth of Pour, Corrosion Resistant Paint
Product Type	Rec CFB, 4 Gang, 3 In, Round Cover, CR
Special Features	Concentric Knock-Outs;Corrosion Resistant;PreGalvanized Stamped Steel Box;Round Cover

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585447308
Manufacturers Part Number	CFB4G30RCR
series	Recessed - CFB Series
UPC	783585447308

Taxonomies, Classifications, and Categories

Category Description	WEATHERPROOF BOXES & COVERS
Type	4-Gang Recessed Floor Box



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 12.25

Uses, Certifications, and Standards

Application For Use in Concrete Floors

Mounting Mounts to Box

standard cULus;UL514