



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CF26DTEIN841 26W 4 Pin Triple Tube Biax GX24Q-3 4100K Compact

*Sylvania-Ledvance*

Catalog Number	CF26DTEIN841
Manufacturer	Sylvania-Ledvance
Description	Dulux 26W Triple Compact Fluorescent Amalgam Lamp With 4 Pin Base, 4100K Color Temperature, 82 Cri, For Use With Electronic and Dimming Ballasts, Ecologic
Weight per unit	0.2300 (lbs/each)
Product Category	Integrated Non-Ballasted Lamps

### Features

amperage rating	Ballast Dependent
average life	16000
Base	GX24q-3
Lamp Type	DULUX T/E
lumens	1,800
Shape	T4
start type	ELECTRONIC RAPID START
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	26

### Material, Color, and Finish

color rendering index (cri)	82
color temperature	4100
Finish	Phosphor Coated

### Dimensions and Weight

Diameter	0.5000000000000000
Length	5

### Descriptions

Description	26W 4 PIN TRIPLE TUBE BIAx GX24Q-3 4100K COMPACT
extra long description	SYL CF26DT/E/IN/841/ECO/20882 CF26D
Long Description	DULUX 26W triple compact fluorescent amalgam lamp with 4 pin base, 4100K color temperature, 82 CRI, for use with electronic and dimming ballasts, ECOLOGIC
Product Type	CF26DTEIN841ECO 50/CS 1/Sku

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135208829
Manufacturers Part Number	CF26DT/E/IN/841/ECO/20882
UPC	046135208829



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... Fluorescent

Type ..... Compact Fluorescent

## Availability

Status ..... Inactive

## Packaging

Carton ..... 1

Package ..... 50

Weight Per each ..... 0.23

## Uses, Certifications, and Standards

Application ..... Commercial/Residential