



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CH140 1P 40A 120V Breaker

*Eaton Corp*

|                  |   |
|------------------|---|
| Catalog Number   | CH140   |
| Manufacturer     | Eaton Corp  |
| Description      | Eaton BR140   Eaton HQP1040   Geindust GTHQL1140   Geindust THQL1140   Geindust THQP140   Grainger 1D243   Grainger 1D345   Ite TL412C   Schneider HOM140   Schneider QO140   Siemens D140   Siemens TL412R1   Squared HOM140   Squared Qo140 |
| Weight per unit  | 0.2000 (lbs/each)   |
| Product Category | 1 Pole Standard Trip Plug-In  |

### Features

|                      |                                   |
|----------------------|-----------------------------------|
| amp                  | 40                                |
| amps                 | 40                                |
| dimensions           | 3.5000 IN X 3.0000 IN X 3.0000 IN |
| interrupt rating     | 10 kAIC                           |
| main circuit breaker | CH                                |
| pole                 | 1                                 |
| pole #               | Single                            |
| Poles                | 1                                 |
| used with            | Type CH Loadcenters               |
| Voltage Rating       | 120/240 V                         |
| Wire Size            | #14-2 AWG Cu/Al                   |

### Dimensions and Weight

|        |     |
|--------|-----|
| Height | 3   |
| Length | 3.5 |
| Width  | 3   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | 1P 40A 120V BREAKER   |
| extra long description | ETN CH140 CH14096-4604-9  |
| Features               | Eaton's residential CH circuit breakers provide premium overload protection. The Type CH circuit breakers trip to the OFF position, eliminating nuisance callbacks. The CHF family also includes a trip flag to differentiate between a trip and the breaker being turned off. The thermal-magnetic trip curve avoids nuisance tripping on mild overloads while reacting almost instantaneously to severe short-circuit conditions. Multiple breakers have an internal common trip connection to operate all poles simultaneous |
| Long Description       | Eaton BR140   Eaton HQP1040   GEIndust GTHQL1140   GEIndust THQL1140   GEIndust THQP140   Grainger 1D243   Grainger 1D345   ITE TL412C   Schneider HOM140   Schneider QO140   Siemens D140   Siemens TL412R1   SquareD HOM140   SquareD QO140   |
| Product Type           | CH14096-4604-9  |

## Manufacturer Information

|                           |                     |
|---------------------------|---------------------|
| Brand                     | EATON CUTLER-HAMMER |
| GTIN                      | 00782113101675      |
| Manufacturers Part Number | CH140               |
| UPC                       | 782113101675        |

## Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | Loadcenter Plug In Breakers and Accessories |
| Type                 | Thermal magnetic circuit breakers           |

## Availability

|                     |          |
|---------------------|----------|
| Manufacturer Status | Inactive |
| Status              | Inactive |

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 0.2 |

## Uses, Certifications, and Standards

|             |  |
|-------------|--|
| Application | Generation - Conventional Energy - Conventional EnergyOtherGeneration - Renewable Energy - Alternative EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - Other |
| standard    | UL 489   |