



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CH2100ST Type CH BRKR100A/2 Pole 120/240V 10K W/Shunt Trip

Eaton Corp

Catalog Number	CH2100ST
Manufacturer	Eaton Corp
Description	Eaton CH Thermal Magnetic Circuit Breaker, Type CH 3/4-Inch Standard Circuit Breaker, 100 A, 10 Kaic, Two-Pole, 120/240V, CH, Common Breaker Trip, #10-1/0 Awg Cu/Al, CH, Type CH Loadcenters, Shunt Trip Included
Weight per unit	0.9000 (lbs/each)
Product Category	2P Special Application Plug-In

### Features

amperage rating	100 A
dimensions	3.5000 IN X 3.5000 IN X 4.4000 IN
interrupt rating	10
Poles	2
Trip Type	Common breaker trip
Voltage Rating	120/240 V

### Descriptions

Description	TYPE CH BRKR100A/2 POLE 120/240V 10K W/SHUNT TRIP
extra long description	ETN CH2100ST CH 100A/2 Pole 120/240
Features	Eaton's residential CH circuit breakers provide premium overload protection. The Type CH circuit breakers trip to the OFF position, eliminating nuisance callbacks. The CHF family also includes a trip flag to differentiate between a trip and the breaker being turned off. The thermal-magnetic trip curve avoids nuisance tripping on mild overloads while reacting almost instantaneously to severe short-circuit conditions. Multiple breakers have an internal common trip connection to operate all poles simultaneous
Long Description	Eaton CH thermal magnetic circuit breaker, Type CH 3/4-Inch standard circuit breaker, 100 A, 10 kAIC, Two-pole, 120/240V, CH, Common breaker trip, #10-1/0 AWG Cu/Al, CH, Type CH Loadcenters, Shunt trip included
Product Type	CH 100A/2 Pole 120/240V 10K
Special Features	Shunt Trip

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113364285
Manufacturers Part Number	CH2100ST
UPC	782113364285



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Specialty Breakers (Quad, Dupl, Shunt Trip)
Type	Thermal magnetic circuit breakers

## Packaging

Carton	1
Weight Per each	0.9

## Uses, Certifications, and Standards

Application	OtherGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyMarine Vessels and Equipment - Marine Vessels and Equipment - OtherDatacenters - IT Space: CI and Hyper Converged
standard	UL 489