



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CH24BPN100E 24C 100A 1PH MB Plug-On Neutral Loadcenter

Eaton Corp

Catalog Number	CH24BPN100E
Manufacturer	Eaton Corp
Description	CH 3/4-Inch Loadcenter, Single-Phase, 24 Circuits, 24-Pole, #2/0-300 Kcmil Wire, 100A, Nema 1
Weight per unit	32.0 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

amperage rating	100 WTT
Box Size	E
cover	Ch8ef-combination, ch8es-surface, not included
Cover Type	Ch8ef-combination, ch8es-surface, not included
dimensions	73.9902centimetreX36.3474centimetreX98.5520millimetre
interrupt rating	25 kAIC
main circuit breaker	CSH
max amps	100
max poles	24
Number of Circuits	24 VDC
number of spaces	24 VDC
Number of Wires	Three-wire
Phase	1 PH
Poles	24-pole
Wire Size	#2/0-300 kcmil

Material, Color, and Finish

Bus Material	Copper
Enclosure Material	Metallic

Dimensions and Weight

Size	E
------	---

Descriptions

Description	24C 100A 1PH MB PLUG-ON NEUTRAL LOADCENTER
extra long description	ETN CH24BPN100E CH 3/4-inch loadcen
Long Description	CH 3/4-inch loadcenter, single-phase, 24 circuits, 24-pole, #2/0-300 kcmil wire, 100A, NEMA 1
Product Type	CH 3/4-Inch Loadcenter
Special Features	Plug-on neutral



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116983360
Manufacturers Part Number	CH24BPN100E
UPC	782116983360

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND
Type	MAIN BREAKER
unspsc code	MODULAR LINE CORD, TELEPHONE LINE EXTENSION CORD TYPE; 15 FT LENGTH IN FT; METALLIC COLOR FAMILY; SILVER MANUFACTURERS COLOR NAME; GC[T] BRAND; CONNECTOR TYPE MODULAR PLUG; CORD SIZE (6) 26 AWG

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	32

Uses, Certifications, and Standards

Enclosure	NEMA 1
standard	UL 67,UL 50