



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CH360ST Type CH BRKR 60A/3 Pole 240V 10K W/Shunt Trip

Eaton Corp

Catalog Number	CH360ST
Manufacturer	Eaton Corp
Description	Eaton CH Thermal Magnetic Circuit Breaker, Type CH 3/4-Inch Standard Circuit Breaker, 60 A, 10 Kaic, Three-Pole, 240V, CH, Common Breaker Trip, #10-1/0 Awg Cu/Al, CH, Type CH Loadcenters, Shunt Trip Included
Weight per unit	1.2 (lbs/each)
Product Category	3 Pole Standard Trip Plug-In

Features

amperage rating	60 A
dimensions	4.8000 IN X 3.5000 IN X 3.5000 IN
interrupt rating	10
Poles	3
Trip Type	Common breaker trip
Voltage Rating	240 V - 240 V

Descriptions

Description	TYPE CH BRKR 60A/3 POLE 240V 10K W/SHUNT TRIP
extra long description	ETN CH360ST CH 60A/3 Pole 240V 10K
Features	Eaton's residential CH circuit breakers provide premium overload protection. The Type CH circuit breakers trip to the OFF position, eliminating nuisance callbacks. The CHF family also includes a trip flag to differentiate between a trip and the breaker being turned off. The thermal-magnetic trip curve avoids nuisance tripping on mild overloads while reacting almost instantaneously to severe short-circuit conditions. Multiple breakers have an internal common trip connection to operate all poles simultaneous
Long Description	Eaton CH thermal magnetic circuit breaker, Type CH 3/4-Inch standard circuit breaker, 60 A, 10 kAIC, Three-pole, 240V, CH, Common breaker trip, #10-1/0 AWG Cu/Al, CH, Type CH Loadcenters, Shunt trip included
Product Type	CH 60A/3 Pole 240V 10K W/Shunt Trip
Special Features	Shunt Trip

Manufacturer Information

Brand	Eaton
GTIN	00782113328379
Manufacturers Part Number	CH360ST
UPC	782113328379



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Specialty Breakers (Quad, Dupl, Shunt Trip)
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	1.15

Uses, Certifications, and Standards

Application	OtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Renewable Energy - Alternative Energy
standard	UL 489