



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CH120AF CH Fireguard AfcI 1 Pole 20 Amp

Eaton Corp

Catalog Number	CH120AF
Manufacturer	Eaton Corp
Description	Eaton CH AfcI Circuit Breaker, Plug-On Branch Feeder Arc Fault Circuit Breaker, 20 A, 10 Kaic, Single-Pole, 120 V or 120/240 V, CH, Type CH Loadcenters
Weight per unit	0.5000 (lbs/each)
Product Category	1P Special Application Plug-In

Features

amperage rating	20 A
interrupt rating	10 kAIC
Poles	Single-pole
Voltage Rating	120/240 V

Dimensions and Weight

Height	3.5
Length	4
Width	.75

Descriptions

Description	CH FIREGUARD AFCI 1 POLE 20 AMP
extra long description	ETN CH120AF Type CH 3/4-inch Fire-G
Features	Eaton's residential CH circuit breakers provide premium overload protection. The Type CH circuit breakers trip to the OFF position, eliminating nuisance callbacks. The CHF family also includes a trip flag to differentiate between a trip and the breaker being turned off. The thermal-magnetic trip curve avoids nuisance tripping on mild overloads while reacting almost instantaneously to severe short-circuit conditions. Multiple breakers have an internal common trip connection to operate all poles simultaneous
Long Description	Eaton CH AFCI circuit breaker, Plug-on branch feeder arc fault circuit breaker, 20 A, 10 kAIC, Single-pole, 120 V or 120/240 V, CH, Type CH Loadcenters
Product Type	Type CH 3/4-Inch Fire-Guard AfcI Circuit Breaker

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114231487
Manufacturers Part Number	CH120AF
UPC	782114231487



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fault Sensing Breakers (AFCI/GFCI)
Type	AFCI circuit breakers

Packaging

Carton	1
Weight Per each	0.5

Uses, Certifications, and Standards

standard	UL Listed
----------	-----------