



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHF125 Type CHF BRKR 25A/1P 120/240V 10 Kaic *Eaton Corp*

Catalog Number	CHF125
Manufacturer	Eaton Corp
Description	Eaton CH Thermal Magnetic Circuit Breaker, Type CHF 3/4-Inch Standard Circuit Breaker, 25 A, 10 Kaic, Single-Pole, 120/240V, CHF, Trip Flag, Common Breaker Trip, (1) #14-8 Awg, (2) #14-10 Awg Cu/Al, CHF, Type CH Loadcenters
Weight per unit	0.3000 (lbs/each)
Product Category	1 Pole Standard Trip Plug-In

Features

dimensions	0.7000 IN X 3.2000 IN X 2.6000 IN
interrupt rating	10 kAIC
Poles	1
Trip Type	Trip flag
Voltage Rating	120/240 V

Descriptions

Description	TYPE CHF BRKR 25A/1P 120/240V 10 KAIC
extra long description	ETN CHF125 CHF BREAKER 25A / 1P 120
Features	Eaton's residential CH circuit breakers provide premium overload protection. The Type CH circuit breakers trip to the OFF position, eliminating nuisance callbacks. The CHF family also includes a trip flag to differentiate between a trip and the breaker being turned off. The thermal-magnetic trip curve avoids nuisance tripping on mild overloads while reacting almost instantaneously to severe short-circuit conditions. Multiple breakers have an internal common trip connection to operate all poles simultaneous
Long Description	Eaton CH thermal magnetic circuit breaker, Type CHF 3/4-Inch standard circuit breaker, 25 A, 10 kAIC, Single-pole, 120/240V, CHF, Trip flag, common breaker trip, (1) #14-8 AWG, (2) #14-10 AWG Cu/Al, CHF, Type CH Loadcenters
Product Type	CHF Breaker 25A / 1P 120/240V 10 Kaic

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685361857
Manufacturers Part Number	CHF125
UPC	786685361857



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Package	10
Weight Per each	0.3

Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative EnergyOtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	UL 489,HACR Rated