

# Eaton CHFCAF120PN

Catalog Number: CHFCAF120PN

Eaton CH AFCI circuit breaker, AFCI Branch feeder circuit breaker, 20 A, 10 kAIC, Single-pole, 120/240 V, CH, Pigtail, Type CH Loadcenters, Plug-on neutral



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH AFCI circuit breaker	CHFCAF120PN
<b>UPC</b>	<b>Product Length/Depth</b>
786685546209	3.5 in
<b>Product Height</b>	<b>Product Width</b>
3 in	1 in
<b>Product Weight</b>	<b>Warranty</b>
0.5 lb	Limited lifetime
<b>Compliances</b>	<b>Certifications</b>
HACR Rated	UL Listed

## Catalog Notes

Switching Duty Rated, HACR Rated

## Product specifications

### Used with

Type CH Loadcenters

### Type

AFCI Branch feeder circuit breaker

### Amperage Rating

20 A

### Voltage rating

120/240 V

### Neutral

Plug-on neutral

### Interrupt rating

10 kAIC

### Main circuit breaker

CH

### Connection

Pigtail

### Number of poles

Single-pole

## Resources

### Catalogs

[Residential and Light Commercial, Metering Products, Volume 1 Tab 4](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHFCAF120PN](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton CHFCAF120PN

Catalog Number: CHFCAF120PN

Eaton CH AFCI circuit breaker, AFCI Branch feeder circuit breaker, 20 A, 10 kAIC, Single-pole, 120/240 V, CH, Pigtail, Type CH Loadcenters, Plug-on neutral



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH AFCI circuit breaker	CHFCAF120PN
<b>UPC</b>	<b>Product Length/Depth</b>
786685546209	3.5 in
<b>Product Height</b>	<b>Product Width</b>
3 in	1 in
<b>Product Weight</b>	<b>Warranty</b>
0.5 lb	Limited lifetime
<b>Compliances</b>	<b>Certifications</b>
HACR Rated	UL Listed

## Catalog Notes

Switching Duty Rated, HACR Rated

## Product specifications

### Used with

Type CH Loadcenters

### Type

AFCI Branch feeder circuit breaker

### Amperage Rating

20 A

### Voltage rating

120/240 V

### Neutral

Plug-on neutral

### Interrupt rating

10 kAIC

### Main circuit breaker

CH

### Connection

Pigtail

### Number of poles

Single-pole

## Resources

### Catalogs

[Residential and Light Commercial, Metering Products, Volume 1 Tab 4](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHFCAF120PN](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)