



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHR8N8N5NS Pop BF 20/20/20, MTRRNGLS, (2) 5-20R2GFI WR, (1) 6 Eaton Corp

Catalog Number	CHR8N8N5NS
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Metered, Pos 1: Non-GND Fault, Pos 2: Non-GND Fault, Pos 3: Non-GND Fault, Circuits: 4, 1, Weather-Resist Center and Left Receptacle, Center: Nema 5-20R2GFI WR, Left: Nema 5-20R2GFI WR, Right: Nema 6-20R2, Ringless
Weight per unit	24.0 (lbs/each)
Product Category	Metered Power Outlet Panels

Dimensions and Weight

Height	8.0000
Length	31.0000
Width	10.0000

Descriptions

Description	POP BF 20/20/20, MTRRNGLS, (2) 5-20R2GFI WR, (1) 6
extra long description	ETN CHR8N8N5NS POP BF 202020 MTRRL(
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount metered, Pos 1: Non-gnd fault, Pos 2: Non-gnd fault, Pos 3: Non-gnd fault, Circuits: 4, 1, Weather-resist center and left receptacle, Center: NEMA 5-20R2GFI WR, Left: NEMA 5-20R2GFI WR, Right: NEMA 6-20R2, Ringless
Product Type	Pop BF 202020 MTRRL(2)520R2GFIWR(1)620R2

Manufacturer Information

Brand	Eaton
GTIN	00786685948461
Manufacturers Part Number	CHR8N8N5NS
UPC	786685948461

Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount metered

Packaging

Carton	1
Weight Per each	24



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

standard

UL Listed