



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CHU9N9NKNS Um Sur Pop 25-20R2GFI WT 16-20R2 W

Eaton Corp

Catalog Number	CHU9N9NKNS
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount, Unmetered, 20A, 20A, 20A, Non-Ground Fault, Non-Ground Fault, Non-Ground Fault, Top, Surface, Circuits: 4, Nema 5-20R2GFI WRTR, Nema 5-20R2GFI WRTR, Nema 6-20R2 WR, 3, 3, 3, 125V, 125V, 250V
Weight per unit	16.4 (lbs/each)
Product Category	Distribution Equipment

### Features

dimensions	6.7000 IN X 9.5000 IN X 17.1000 IN
------------	------------------------------------

### Dimensions and Weight

Depth	6.7000
Height	17.1000
Width	9.5000

### Descriptions

Description	UM SUR POP 25-20R2GFI WT 16-20R2 W
extra long description	ETN CHU9N9NKNS UM SUR POP (2)5-20R2
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount, Unmetered, 20A, 20A, 20A, Non-ground fault, Non-ground fault, Non-ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2GFI WRTR, NEMA 5-20R2GFI WRTR, NEMA 6-20R2 WR, 3, 3, 3, 125V, 125V, 250V
Product Type	Um Sur Pop (2)5-20R2GFI WT (1)6-20R2 W
Special Features	Pedestal Mount

### Manufacturer Information

Brand	Eaton
GTIN	00786689321321
Manufacturers Part Number	CHU9N9NKNS
UPC	786689321321

### Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount unmetered



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	16.42

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	SURFACE
standard	UL 231,UL Listed file E163588