



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CI355 Pir Ceiling Occ Sensor 100-347VAC Center Mount 360 *Wattstopper*

Catalog Number	CI355
Manufacturer	Wattstopper
Description	Wattstopper'S Ci-355 Passive Infrared (Pir) Occupancy Sensor Automatically Turns Lighting On and Off Based On Occupancy.
Weight per unit	0.4500 (lbs/each)
Product Category	Lighting Occupancy Sensors

Features

body	Plastic
Connection Type	Wired
included	Mounting Screws, Sensor Mask
indicator	LED Light
indoor/outdoor	Indoor
Input Voltage	120/230/277/347 VAC
load	Magnetic Low Voltage
Mounting Type	Surface, 2-1/4 in Deep J-Box
Number of Connections	4.0
Sensor Type	Occupancy
supply voltage	120/230/277/347
Switch Type	Motion Sensor
Voltage	277.0 V, 100.0 V, 347.0 V
Wattage	800.0
Wire Size	#14 - #10 Awg

Descriptions

Description	PIR CEILING OCC SENSOR 100-347VAC CENTER MOUNT 360
extra long description	P&S CI355 PIR-CELNG OCC SNSR 100-34
Features	IR (Infrared), Motion Sensor
Long Description	Wattstopper's CI-355 passive infrared (PIR) occupancy sensor automatically turns lighting on and off based on occupancy.
Product Type	Pir-Celng Occ SNSR 100-347 Vac, 360
Special Features	Passive Infrared/Line Voltage

Manufacturer Information

Brand	Legrand-Wattstopper
GTIN	00754182914333
Manufacturers Part Number	CI355
UPC	754182914333



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	SWITCH

Packaging

Carton	1
Weight Per each	0.45

Uses, Certifications, and Standards

Application	Office Spaces, Classrooms, Warehouses
environmental conditions	120
Mounting	WALL
nema rating	WD 7-2000
standard	ROHS, UL, cUL