ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CIRS Led Single Remote Head White

Hubbell Lighting/Current Hli

Catalog Number	CIRS
Manufacturer	Hubbell Lighting/Current Hli
Description	N/A, Mounting Type: Wall, Ceiling, End Mount, Face Style: Universal Single/Double Face, Wording On Sign: Exit, Letter Color: Red, Color: White, Number Of Lamps: 0, Operation: Emergency Operation, Battery Type: Lead-Calcium, Battery Runtime: 90 Min, Voltage Rating: 120/277 Vac.
Weight per unit	1.0 (lbs/each)
Product Category	Emergency Lighting, Exit Signs

Features

battery	Lead-Calcium
Battery Type	Lead-Calcium
exact weight	1
Fixture Type	Emergency Lighting
Lamp Type	none
Lamp Wattage	4.5
Number of Lamps	0
Voltage Rating	120/277 VAC
Wattage	4.5

Material, Color, and Finish

Color	White
housing color	White
Letter Color	RED

Dimensions and Weight

Size	6.7 Inch W x 2.5 Inch D x 4.7 Inch H

Descriptions

Description	LED SINGLE REMOTE HEAD WHITE
extra long description	
Long Description	N/A, Mounting Type: Wall, ceiling, end mount, Face style: Universal Single/Double Face, Wording On Sign: EXIT, Letter Color: Red, Color: White, Number of Lamps: 0, Operation: emergency operation, Battery Type: Lead-Calcium, Battery Runtime: 90 min, Voltage Rating: 120/277 VAC.
Product Type	Emergency Remote Head

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	COMPASS
GTIN	00782520862022
Manufacturers Part Number	CIRS
UPC	782520862022

Taxonomies, Classifications, and Categories

Category Description	Emergency Lighting, Exit Signs & Inverters
	Emergency Lighting
Type	Single Remote Head

Packaging

Carton	1
Weight Per each	1

Uses, Certifications, and Standards

Application	Manufacturing;Warehouse;Offices;Hospitality;Quick Service Restaurants;Retail;Automotive Dealers;Educational;Healthcare
Mounting	Wall, ceiling, end mount
standard	UL 924 Listed