



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CHP42B225R CH Pon Loadcntr 225A Main BRKR 42 Space N3R

Eaton Corp

Catalog Number	CHP42B225R
Manufacturer	Eaton Corp
Description	Eaton CH Main Breaker Loadcenters, Cover Included, Main Breaker, 225 A, X7, Copper, Nema 3R, Metallic, CSR, 84, 42, Three-Wire, Single-Phase, Overhead, 120/240 V
Weight per unit	33.0 (lbs/each)
Product Category	Single Phase Main Breaker Load

### Features

amperage rating	225
media	Yes
number of spaces	42
Phase	1
Voltage Rating	120/240 V

### Dimensions and Weight

Depth	37
Height	5.19
Size	X7
Width	14.31

### Descriptions

Description	CH PON LOADCNTR 225A MAIN BRKR 42 SPACE N3R
extra long description	ETN CHP42B225R CH PON LC, 225A, MB,
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH main breaker loadcenters,Cover included,Main breaker,225 A,X7,Copper,NEMA 3R,Metallic,CSR,84,42,Three-wire,Single-phase,Overhead,120/240 V
Product Type	CH Pon LC, 225A, MB, 42SP, N3R
Special Features	Cover included



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Eaton
GTIN	00786689058722
Manufacturers Part Number	CHP42B225R
UPC	786689058722

## Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Main breaker loadcenter

## Packaging

Carton	1
Weight Per each	33

## Uses, Certifications, and Standards

Application	Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	UL 50,UL 67