



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CLT50NC630 Corg Loom TBG *Panduit Corporation*

Catalog Number	CLT50NC630
Manufacturer	Panduit Corporation
Description	The CLT50N-C630 Corrugated Loom Slit Wall Tubing Protects Cables From Impact and Abrasion. Features A Slit For Easy Installation Onto A Bundle Of Wires or A Pre-Assembled Harness Assembly, Increasing Productivity. Hold In Place With Cable Ties and Accessories. Suitable For Indoor Applications. UL94-HB Flammability Rating and A Maximum Temperature Rating Of 230°F (110°C). Heat-Stabilized Nylon 6. Inside Diameter 0.5081" (13.16MM). Color HS Black. 1 Per Package.
Weight per unit	3.5 (lbs/each)
Product Category	Cable Ties & Wraps

### Features

Inside Diameter	0.518
Material	NYLON 6
media	Yes
outside diameter	0.67

### Material, Color, and Finish

Color	Black
-------	-------

### Dimensions and Weight

Length	100
--------	-----

### Descriptions

Description	CORG LOOM TBG
extra long description	PAN CLT50N-C630 Corr. Loom Tubing N
Long Description	The CLT50N-C630 Corrugated Loom Slit Wall Tubing protects cables from impact and abrasion. Features a slit for easy installation onto a bundle of wires or a pre-assembled harness assembly, increasing productivity. Hold in place with cable ties and accessories. Suitable for indoor applications. UL94-HB flammability rating and a maximum temperature rating of 230°F (110°C). Heat-Stabilized Nylon 6. Inside diameter 0.5081" (13.16mm). Color HS Black. 1 per package.
Product Type	Corr. Loom Tubing Nylon, .5" (12.7MM) X 100', HS Black, PK1



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	PANDUIT
GTIN	00074983287185
Manufacturers Part Number	CLT50N-C630
UPC	074983287185

## Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Corrugated Loom Tubing

## Packaging

Carton	10
Package	4
Weight Per each	3.5499

## Uses, Certifications, and Standards

Application	Covers wire and cable to protect from abrasion
standard	RoHS Compliant
Temperature Rating	230