



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CS115GY Switch Toggle SP 15A 120/277V Swire Gy

Eaton Wiring Devices

Catalog Number	CS115GY
Manufacturer	Eaton Wiring Devices
Description	Eaton Commercial Grade Toggle Switch, #14-10 Awg, 15A, Commercial, Flush, 120/277V, Side Wire, Screw, Gray, Load Type: Motor Control, Fan, Led, Incandescent, Elv, MLV, CFL, Flourescent, Halogen, Single-Pole, Single-Pole, Brass, PVC
Weight per unit	0.1100 (lbs/each)
Product Category	Gen Purpose Switches

Features

amperage rating	15
dimensions	1.3000 IN X 0.9020 IN X 4.2000 IN
Material	PVC
Poles	1
Voltage Rating	120/277 V

Descriptions

Description	SWITCH TOGGLE SP 15A 120/277V SWIRE GY
extra long description	EWD CS115GY Switch Toggle SP 15A 12
Features	Eaton's Arrow Hart commercial specification grade switches are designed to provide superior quality, reliability and performance in a variety of commercial environments.
Long Description	Eaton commercial grade toggle switch, #14-10 AWG, 15A, Commercial, Flush, 120/277V, Side wire, Screw, Gray, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, Single-Pole, Single-Pole, Brass, PVC
Product Type	Switch Toggle SP 15A 120/277V Swire Gy
Special Features	Commercial Grade

Manufacturer Information

Brand	Eaton
GTIN	00032664487484
Manufacturers Part Number	CS115GY
UPC	032664487484

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	Commercial grade toggle switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Package	50
Weight Per each	0.11

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	Federal Specification Classification 6241 05,cULus Listed,NOM