



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CPX2X2AL07SWW7M4 2X2 Led Flat Panel Kelvin/Lumen Select 35K/4K/5K

*Lithonia Lighting - Acuity*

Catalog Number	CPX2X2AL07SWW7M4
Manufacturer	Lithonia Lighting - Acuity
Description	The 2 FT. X 2 FT. CPX Panel From Lithonia Lighting Is The Perfect Choice For A Quality Led Panel At An Affordable Price. The Smooth, Even Lens Projects A Crisp and Clean Aesthetic. This CPX Configuration Offers Adjustable Light Output (Alo) For The Option Of 2400-4200 Lumens and Switchable White (SWW) For Three Color Temperature In One - 35/40/50K CCT. CPX Is The Perfect Choice For Budget-Conscious School, Commercial Office, or Small Retail Footprint Projects.
Weight per unit	7.7 (lbs/each)
Product Category	Lighting

### Features

average life	60
connection	Hardwired
dimensions	23.875 x 23.875 x 1.68
Fixture Type	Flat Panel
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Dynamic
lumens	2500 ,3200 ,4000 ,Switchable
Material	Steel
Power Source	Hardwired
Shape	Square
Voltage Rating	120-277
Warranty	5
Wattage	37.5

### Material, Color, and Finish

Color	White
Finish	Semi-Gloss
Lens Color	WHITE
Style	Traditional

### Dimensions and Weight

Height	1.7
Length	23.8
Size	23.87 5x 23.875 x 1.68
Width	23.8



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Construction	New Construction,Remodel
Description	2X2 LED FLAT PANEL KELVIN/LUMEN SELECT 35K/4K/5K
extra long description	LITH CPX 2X2 ALO7 SWW7 M4 LED Flat
Features	Contractor Select
Long Description	The 2 ft. x 2 ft. CPX panel from Lithonia Lighting is the perfect choice for a quality LED panel at an affordable price. The smooth, even lens projects a crisp and clean aesthetic. This CPX configuration offers Adjustable Light Output (ALO) for the option of 2400-4200 lumens and Switchable White (SWW) for three color temperature in one - 35/40/50K CCT. CPX is the perfect choice for budget-conscious school, commercial office, or small retail footprint projects.
Product Type	Flat Panel

## Manufacturer Information

Brand	Lithonia Lighting
GTIN	00193048542806
Manufacturers Part Number	CPX 2X2 ALO7 SWW7 M4
UPC	193048542806

## Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Flat Panel

## Trade Size

aperture size	2x2
---------------	-----

## Packaging

Carton	1
Package	4
Weight Per each	7.72

## Uses, Certifications, and Standards

Application	Education,Government,Hospitality,House of Worship,Offices & Banks,Residential,Retail
environmental conditions	Indoor
Mounting	Recessed,Surface,Suspended
standard	CSADLC Premium,DLC Standard