



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CS6375 LKG Inlt, 50A 125/250V, 3P4W *Hubbell Wiring Devices*

| | |
|------------------|--|
| Catalog Number | CS6375 |
| Manufacturer | Hubbell Wiring Devices |
| Description | Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 50A, 125V/250V Ac, 3-Pole 4-Wire Grounding, Non-Nema, Screw Terminal, Steel |
| Weight per unit | 0.8500 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|---------------------|---------------------------|
| amperage rating | 50 |
| connection | Pressure Screw Terminals |
| Current Rating | 50 |
| Dielectric Strength | Withstands 2,000V minimum |
| Material | Steel, Zinc Plated |
| Number of Wires | 4-Wire |
| pallet quantity | 810 |
| Phase | 1 |
| Poles | 3-Pole |
| Voltage Rating | 125/250 VAC |
| Wattage | 12,500 |
| Wire Size | #10 to #6 |

Material, Color, and Finish

| | |
|-------|----------|
| Color | Metallic |
|-------|----------|

Dimensions and Weight

| | |
|------|-----------------------------|
| Size | 2.17 in x 3.50 in x 2.62 in |
|------|-----------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | LKG INLT, 50A 125/250V, 3P4W |
| extra long description | HWDK CS6375 LKG INLT, 50A 125/250V, |
| Features | Hubbell's 50 Amp Twist-Lock® Devices feature a heavy-duty design and super-tough nylon housing built for heavy-duty applications and impact resistance, even in the harshest environments. Their rigid construction restricts contact distortion, minimizing the possibility of mating dissimilar devices. The cord grip's offset gripping jaws securely hold the conductors and the cord jacket for excellent strain relief. |
| Long Description | Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 50A, 125V/250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Steel |
| Product Type | LKG Inlt, 50A 125/250V, 3P4W |
| Special Features | Standard Product |

Manufacturer Information

| | |
|---------------------------|-----------------------|
| Brand | WIRING DEVICE-KELLEMS |
| GTIN | 00783585828206 |
| Manufacturers Part Number | CS6375 |
| UPC | 783585828206 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES |
| Type | Flanged Inlet |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.85 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Extra Heavy Duty Industrial |
| environmental conditions | Indoor Dry unless protected by additional means |
| Mounting | Screw Mount |
| nema rating | Non-NEMA |
| standard | Certified to CSA C22.2 No.42;Listed to UL 498 |