

Specifications

Eaton CRC3033BC

Eaton Crouse-Hinds series PowerMate CRC connector, 30A, 0.390-1.375", Three-wire, three-pole, Style 1, Copper-free aluminum, 600 Vac/250 Vdc



Photo is representative

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series PowerMate CRC connector
CATALOG NUMBER	CRC3033BC
UPC	662276276376
PRODUCT LENGTH/DEPTH	6.6 in
PRODUCT HEIGHT	2.56 in
PRODUCT WIDTH	2.56 in
PRODUCT WEIGHT	2.2 lb



Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

AMPERAGE RATING 30A

	Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4X

GROUNDING TYPE	Style 1
CONFIGURATION	Three-wire, three-pole
CABLE DIAMETER	0.390-1.375"
VOLTAGE RATING	600 Vac/250 Vdc
MATERIAL	Copper-free aluminum

Resources

3D CAD DRAWING PACKAGE [Eaton Crouse-Hinds CRC3033BC 3D drawing](#)

BROCHURES [PowerMate Drilling Pin and Sleeve Devices brochure](#)

CATALOGS [PowerMate Drilling Pin and Sleeve Devices catalog page](#)

CERTIFICATION REPORTS [PowerMate Drilling Pin and Sleeve Devices cUL certification \(Plugs and Connectors\)](#)

[PowerMate Drilling Pin and Sleeve Devices UL certification \(Plugs and Connectors\)](#)

INSTALLATION INSTRUCTIONS [IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

SPECIFICATIONS AND DATASHEETS [PowerMate Connectors](#)

[Eaton Specification Sheet - CRC3033BC](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications

Eaton CRC3033BC

Eaton Crouse-Hinds series PowerMate CRC connector, 30A, 0.390-1.375", Three-wire, three-pole, Style 1, Copper-free aluminum, 600 Vac/250 Vdc



Photo is representative

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series PowerMate CRC connector
CATALOG NUMBER	CRC3033BC
UPC	662276276376
PRODUCT LENGTH/DEPTH	6.6 in
PRODUCT HEIGHT	2.56 in
PRODUCT WIDTH	2.56 in
PRODUCT WEIGHT	2.2 lb



Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

AMPERAGE RATING 30A

	Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4X

GROUNDING TYPE	Style 1
CONFIGURATION	Three-wire, three-pole
CABLE DIAMETER	0.390-1.375"
VOLTAGE RATING	600 Vac/250 Vdc
MATERIAL	Copper-free aluminum

Resources

3D CAD DRAWING PACKAGE

[Eaton Crouse-Hinds CRC3033BC 3D drawing](#)

BROCHURES

[PowerMate Drilling Pin and Sleeve Devices brochure](#)

CATALOGS

[PowerMate Drilling Pin and Sleeve Devices catalog page](#)

CERTIFICATION REPORTS

[PowerMate Drilling Pin and Sleeve Devices cUL certification \(Plugs and Connectors\)](#)

[PowerMate Drilling Pin and Sleeve Devices UL certification \(Plugs and Connectors\)](#)

INSTALLATION INSTRUCTIONS

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

SPECIFICATIONS AND DATASHEETS

[PowerMate Connectors](#)

[Eaton Specification Sheet - CRC3033BC](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

