



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CSB15AC1I 15A 120/277VAC B+S Wire Comm SP SW Iv *Pass & Seymour/Legrand*

| | |
|------------------|---|
| Catalog Number | CSB15AC1I |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Construction 1-Pole Switch, Back and Side-Wire, 15A 120/277V. |
| Weight per unit | 0.1711 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------|-------------------|
| action | SP |
| amperage rating | 15 |
| Contact Rating | 15amp, 120/277vac |
| insulation | False |
| Poles | Single Pole |
| Switch Type | Toggle |
| Voltage | 120.0 V |
| Voltage Rating | 120/277 |

Dimensions and Weight

| | |
|------|------|
| Size | 3.3" |
|------|------|

Descriptions

| | |
|------------------------|--|
| Description | 15A 120/277VAC B+S WIRE COMM SP SW IV |
| extra long description | P&S CSB15AC1I 15A 120/277VAC B+S WI |
| Long Description | Construction 1-Pole Switch, Back and Side-Wire, 15A 120/277V. |
| Product Type | 15A 120/277VAC B+S Wire Comm SP SW I |
| Special Features | Back & Side wire, locking support, one piece brass alloy contact arm |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007126020 |
| Manufacturers Part Number | CSB15AC1-I |
| UPC | 785007126020 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | Industrial receptacles |
| Type | SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 50 |
| Weight Per each | 0.1711 |

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Commercial/Residential |
| Mounting | WALL |
| standard | CULUS, FEDSPEC, UL20 |