



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CSD201610SS 20X16X10 N4X SS4 HC QTR TRN LTCH

Hoffman Enclosures, Inc.

| | |
|------------------|--|
| Catalog Number | CSD201610SS |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Concept Wallmount 1/4-Turn Latch Type 4X, 20X16X10, Brushed, Stainless 304 |
| Weight per unit | 28.0 (lbs/each) |
| Product Category | Nema Types 4 & 4X Metallic Enc |

Features

| | |
|-----------|---------------------|
| ip rating | IP66 |
| Material | Stainless Steel 304 |

Material, Color, and Finish

| | |
|--------|--------------|
| Color | Unpainted |
| Finish | Brushed #4 |
| Style | Quarter-turn |

Dimensions and Weight

| | |
|--------|----------------------|
| Depth | 10 |
| Height | 20 |
| Size | 20.00x16.00x10.00 in |
| Width | 16 |

Descriptions

| | |
|------------------------|--|
| Description | 20X16X10 N4X SS4 HC QTR TRN LTCH |
| extra long description | NVENT HOF CSD201610SS Wall Mount Ty |
| Features | For indoor or outdoor applications that require corrosion protection from chemicals and water. Concept Enclosures feature streamlined styling with an attractive stroked finish and flush quarter-turn latches for secure closure. |
| Long Description | Concept Wallmount 1/4-Turn Latch Type 4X, 20x16x10, Brushed, Stainless 304 |
| Product Type | Wall Mount Type 4X Enclosure |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510128586 |
| Manufacturers Part Number | CSD201610SS |
| UPC | 783510128586 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | STEEL JUNCTION BOXES |
| Type | Stainless Steel Wall Mounted Industrial Enclosures |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 28 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Corrosive Environments; Controls and Drives |
| nema rating | 4X Watertight, corrosion-resistant |