



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CS8369 Locking RCPT, 50A 3PH 250V, 3P4W Hubbell Wiring Devices

Catalog Number	CS8369
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Industrial, Receptacle, 50A 3-Phase Delta 250V Ac, 3-Pole 4-Wire Grounding, Non-Nema, Screw Terminal, Black
Weight per unit	0.2150 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	50
connection	Screw Terminal
Current Rating	50
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	4-Wire
pallet quantity	1680
Phase	3
Poles	3-Pole
Voltage Rating	3-Phase Delta 250 VAC
Wattage	12,500
Wire Size	#10 to #6

Dimensions and Weight

Size	2.69 in x 2.12 in x 2.36 in
------	-----------------------------

Descriptions

Description	LOCKING RCPT, 50A 3PH 250V, 3P4W
extra long description	HWDK CS8369 LOCKING RCPT, 50A 3PH 2
Features	Hubbell's 50 Amp Twist-Lock® Devices feature a heavy-duty design and super-tough nylon housing built for heavy-duty applications and impact resistance, even in the harshest environments. Their rigid construction restricts contact distortion, minimizing the possibility of mating dissimilar devices. The cord grip's offset gripping jaws securely hold the conductors and the cord jacket for excellent strain relief.
Long Description	Locking Devices, Twist-Lock®, Industrial, Receptacle, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black
Product Type	Locking RCPT, 50A 3PH 250V, 3P4W
Special Features	Standard Product



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585829074
Manufacturers Part Number	CS8369
UPC	783585829074

Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	RECEPTACLE

Packaging

Carton	1
Weight Per each	0.215

Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	Non-NEMA
standard	Certified to CSA C22.2 No.42;Listed to UL 498