



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

CT103 #6 C Taps

Nsi Industries

Catalog Number	CT103
Manufacturer	Nsi Industries
Description	Copper C Tap Grounding Connector For 6 to 8 Awg Copper "C" Taps Ensure Positive, All Around Compression With Low-Resistance and High Pull-Out Values. Made Of High Conductivity Copper, They Satisfy The Requirements Of NEC250-81 and 250-91 For Connecting to The Grounding Electrode System. Rated 600 Volts.
Weight per unit	0.0100 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Conductor Size	6 AWG
Material	Copper
Tap Size	12 AWG
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Gray
Finish	COPPER

Dimensions and Weight

Size	6-12 AWG
------	----------

Descriptions

Description	#6 C TAPS
extra long description	NSI CT-103 Copper C Tap 6-8 Main
Features	Copper C Tap Grounding Connector for 6 to 8 AWG Copper "C" Taps ensure positive, all around compression with low-resistance and high pull-out values. Made of high conductivity copper, they satisfy the requirements of NEC250-81 and 250-91 for connecting to the grounding electrode system. Rated 600 Volts.
Long Description	Copper C Tap Grounding Connector for 6 to 8 AWG Copper "C" Taps ensure positive, all around compression with low-resistance and high pull-out values. Made of high conductivity copper, they satisfy the requirements of NEC250-81 and 250-91 for connecting to the grounding electrode system. Rated 600 Volts.
Product Type	Copper C Tap 6-8 Main
Special Features	6-12 AWG



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	NSi
GTIN	00662381098023
Manufacturers Part Number	CT-103
UPC	662381098023

Taxonomies, Classifications, and Categories

Category Description	T&B C TAP LUGS
Type	C-Taps

Packaging

Carton	1
Package	100
Weight Per each	0.01

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
standard	UL486
Temperature Rating	90 C