



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CTH46 Heavy Duty Copper C Tap Grounding Connector For 6

*Nsi Industries*

Catalog Number	CTH46
Manufacturer	Nsi Industries
Description	Heavy Duty Copper C Tap Grounding Connector For 6 to 4 Awg Run - 4-4 Awg Tap Applications: Copper "C" Taps Are Range-Taking Compression Connectors Made From High Conductivity Copper Alloy. Ideal For Making Tap or Parallel Copper Connections From 8 Sol to 4/0 STR Conductors. Provides Consistent Reliability With Heavy Wall Construction That Prevents Relaxation Of The Joint After Installation. Installation Time Is Reduced Because Of Its "C" Shape. Ul CU486A, 467 Suitable For Direct Burial.
Weight per unit	0.0340 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Conductor Size	(Run) 6 SOL-4 STR
Material	Copper
Tap Size	6 SOL-6 STR
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Copper
Finish	COPPER

### Dimensions and Weight

Size	L=.625 - W=.437 - H=.750
------	--------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	HEAVY DUTY COPPER C TAP GROUNDING CONNECTOR FOR 6
extra long description	NSI CTH-46 Copper C Tap 6-4 Main 6-
Features	Heavy Duty Copper C Tap Grounding Connector for 6 to 4 AWG Run - 4-4 AWG Tap APPLICATIONS: Copper "C" Taps are range-taking compression connectors made from high conductivity copper alloy. Ideal for making tap or parallel copper connections from 8 SOL to 4/0 STR conductors. Provides consistent reliability with heavy wall construction that prevents relaxation of the joint after installation. Installation time is reduced because of its "C" shape. UL CU486A, 467 suitable for direct burial.
Long Description	Heavy Duty Copper C Tap Grounding Connector for 6 to 4 AWG Run - 4-4 AWG Tap APPLICATIONS: Copper "C" Taps are range-taking compression connectors made from high conductivity copper alloy. Ideal for making tap or parallel copper connections from 8 SOL to 4/0 STR conductors. Provides consistent reliability with heavy wall construction that prevents relaxation of the joint after installation. Installation time is reduced because of its "C" shape. UL CU486A, 467 suitable for direct burial.
Product Type	Copper C Tap 6-4 Main 6-6 Tap
Special Features	(Run) 6 SOL-4 STR - (Tap) 6 SOL-6 STR

## Manufacturer Information

Brand	NSi
GTIN	00662381022141
Manufacturers Part Number	CTH-46
UPC	662381022141

## Taxonomies, Classifications, and Categories

Type	Copper C Taps
------	---------------

## Packaging

Carton	1
Weight Per each	0.034

## Uses, Certifications, and Standards

Application	Terminate-Splice-Tap
environmental conditions	90 C
Temperature Rating	90 C