



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **D2139 Lineman'S Pliers, New England Nose, 9"** *Klein Tools*

Catalog Number	D2139
Manufacturer	Klein Tools
Description	These High-Leverage, Side-Cutting Pliers Feature A Square Nose For Twisting and Grabbing Wires. The Rivet Is Closer to The Cutting Edge For 46-Percent More Cutting and Gripping Power Than Other Pliers. Induction Hardened Cutting Knives Are Extra Durable For Longer Life. The Exclusive Handle Tempering Absorbs The Snap When Cutting Wire. Forged From Custom Us-Made Steel For Maximum Durability.
Weight per unit	1.2 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

### **Features**

Handle Length	5.41" (13.7 cm)
Jaw Length	1.91" (4.9 cm)
jaw thickness	0.62" (1.6 cm)
Jaw Width	1.24" (3.1 cm)
knife length	0.781" (2 cm)
Material	Induction Hardened Steel
media	Yes
Overall Width	2.06" (5.2 cm)
tether capable	No

### **Material, Color, and Finish**

Handle Color	dark blue
--------------	-----------

### **Dimensions and Weight**

Overall Length	9.35" (23.7 cm)
----------------	-----------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	LINEMAN'S PLIERS, NEW ENGLAND NOSE, 9"
extra long description	KLEIN D213-9 High Lev. Pliers, Side
Features	These High-Leverage, Side-Cutting Pliers feature a square nose for twisting and grabbing wires. The rivet is closer to the cutting edge for 46-Percent more cutting and gripping power than other pliers. Induction hardened cutting knives are extra durable for longer life. The exclusive handle tempering absorbs the snap when cutting wire. Forged from custom US-made steel for maximum durability.
Long Description	These High-Leverage, Side-Cutting Pliers feature a square nose for twisting and grabbing wires. The rivet is closer to the cutting edge for 46-Percent more cutting and gripping power than other pliers. Induction hardened cutting knives are extra durable for longer life. The exclusive handle tempering absorbs the snap when cutting wire. Forged from custom US-made steel for maximum durability.
Product Type	High Lev. Pliers, Side Cut, SQ, 9"

## Manufacturer Information

Brand	Klein Tools
GTIN	00092644700385
Manufacturers Part Number	D213-9
UPC	092644700385

## Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Side Cutting Pliers

## Packaging

Carton	1
Weight	1.0 lb (0.5 kg)
Weight Per each	1.16

## Uses, Certifications, and Standards

Application	#8 AWG Copper, Aluminum and Other Soft Metals
standard	Y