



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



D2288INS Diagonal Cutting Pliers, Insulated, High Leverage

Klein Tools

Catalog Number	D2288INS
Manufacturer	Klein Tools
Description	These High-Leverage Insulated Diagonal-Cutting Pliers Are 1000V Rated For Safety On The Job. The Thick, Exceptionally Tough White Inner Layer Coating Is Bonded To The Tool. Integral Thumb Guards Prevent Hand Contact With Conductive Parts. The Bright Orange Handles Make This Tool Comfortable to Use All Day and Easy to Identify In The Field. The Durable, Molded Insulation Meets or Exceeds IEC 60900 and Astm F1505 Standards For Insulated Tools. Cutting Knives Are Induction Hardened For Long Life.
Weight per unit	0.7000 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

Features

Handle Length	4.9" (12.4 cm)
Jaw Length	0.781" (2 cm)
jaw thickness	0.46" (1.2 cm)
Jaw Width	1.25" (3.2 cm)
knife length	0.188 (0.5 cm)MaterialSteelOverall Length4.25 (10.8 cm)
Material	Induction Hardened Steel
tether capable	No

Material, Color, and Finish

Handle Color	ORANGE
--------------	--------

Dimensions and Weight

Overall Length	8.24" (20.9 cm)
----------------	-----------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	DIAGONAL CUTTING PLIERS, INSULATED, HIGH LEVERAGE
extra long description	KLEIN D228-8-INS 8" Insulated, Diag
Features	These High-Leverage Insulated Diagonal-Cutting pliers are 1000V rated for safety on the job. The thick, exceptionally tough white inner layer coating is bonded to the tool. Integral thumb guards prevent hand contact with conductive parts. The bright orange handles make this tool comfortable to use all day and easy to identify in the field. The durable, molded insulation meets or exceeds IEC 60900 and ASTM F1505 standards for insulated tools. Cutting knives are induction hardened for long life.
Long Description	These High-Leverage Insulated Diagonal-Cutting pliers are 1000V rated for safety on the job. The thick, exceptionally tough white inner layer coating is bonded to the tool. Integral thumb guards prevent hand contact with conductive parts. The bright orange handles make this tool comfortable to use all day and easy to identify in the field. The durable, molded insulation meets or exceeds IEC 60900 and ASTM F1505 standards for insulated tools. Cutting knives are induction hardened for long life.
Product Type	8" Insulated, Diagonal-Cutters
Special Features	Flame Retardant and Impact Resistant Handle

Manufacturer Information

Brand	Klein Tools
GTIN	00092644720420
Manufacturers Part Number	D2288INS
UPC	092644720420

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Diagonal Cutting Pliers

Packaging

Carton	1
Package	3
Weight	11.2 oz (318 g)
Weight Per each	0.7

Uses, Certifications, and Standards

Application	ACSR, Screws, Nails and Most Hardened Wire
Configuration	Tapered Nose
standard	IEC 60900 and ASTM F1505