

# KLAW™ PUMP PLIERS

**Unique jaw design**  
provides multiple points of  
contact for maximum torque  
and grip.



**Classic**



**Quick-Adjust**

For Professionals... Since 1857®

**KLEIN  
TOOLS®**





Wider Jaw Opening



More Gripping Teeth



Nail Holding Groove

## Grasp the Klein Difference!

### Klein Tools Klaw™ Pump Pliers

Get a better grip on the job at hand with Klein Tools Klaw™ Pump Pliers.

The uniquely designed jaw provides multiple points of contact for maximum torque. Specially hardened teeth cover the inside of the jaw for excellent gripping power. The 10" and 12" sizes also feature a groove near the jaw tip designed especially for holding nails.

Klaw™ Pump Pliers are available in a Classic style or a Quick-Adjust style that features a push button, quick ratchet feature for faster, easier adjustment.



### KLAW™ Pump Pliers



Quick-Adjust



Classic

- **Push button and quick ratchet feature allows for fast and easy adjustment to any position.**  
(Cat. Nos. D504-10B, D504-12B)
- **Compact, narrow design for easy work in small or hard to reach spaces.**
- **Gripping surfaces with specially hardened teeth for reduced wear and positive gripping.**
- **Extended grips for added comfort.**

Cat. No.	Overall Length	Max. Jaw Capacity	Handle Finish	Handle Color	Weight
<b>Quick-Adjust Pump Pliers</b>					
D504-10B	10-1/8" (257 mm)	2-1/8" (54 mm)	plastic-dipped	yellow	.79 lbs. (0.36 kg)
D504-12B	12-1/2" (318 mm)	2-3/4" (70 mm)	plastic-dipped	yellow	1.2 lbs. (0.54 kg)
<b>Classic Pump Pliers</b>					
D504-7	7-3/8" (187 mm)	1-3/8" (35 mm)	plastic-dipped	yellow	.34 lbs. (0.15 kg)
D504-10	9-7/8" (250 mm)	2-1/8" (54 mm)	plastic-dipped	yellow	.81 lbs. (0.37 kg)
D504-12	12" (305 mm)	2-3/4" (70 mm)	plastic-dipped	yellow	1.4 lbs. (0.64 kg)



See our complete line of Pump Pliers

[www.kleintools.com](http://www.kleintools.com)



© 2013 Klein Tools, Inc.  
Lincolnshire, IL, 60069-1418  
Printed in U.S.A. 96163



# KLAW™ PUMP PLIERS

**Unique jaw design**  
provides multiple points of  
contact for maximum torque  
and grip.



**Classic**



**Quick-Adjust**

For Professionals... Since 1857®

**KLEIN  
TOOLS®**





Wider Jaw Opening



More Gripping Teeth



Nail Holding Groove

## Grasp the Klein Difference!

### Klein Tools Klaw™ Pump Pliers

Get a better grip on the job at hand with Klein Tools Klaw™ Pump Pliers.

The uniquely designed jaw provides multiple points of contact for maximum torque. Specially hardened teeth cover the inside of the jaw for excellent gripping power. The 10" and 12" sizes also feature a groove near the jaw tip designed especially for holding nails.

Klaw™ Pump Pliers are available in a Classic style or a Quick-Adjust style that features a push button, quick ratchet feature for faster, easier adjustment.



### KLAW™ Pump Pliers



Quick-Adjust



Classic

- **Push button and quick ratchet feature allows for fast and easy adjustment to any position.**  
(Cat. Nos. D504-10B, D504-12B)
- **Compact, narrow design for easy work in small or hard to reach spaces.**
- **Gripping surfaces with specially hardened teeth for reduced wear and positive gripping.**
- **Extended grips for added comfort.**

Cat. No.	Overall Length	Max. Jaw Capacity	Handle Finish	Handle Color	Weight
<b>Quick-Adjust Pump Pliers</b>					
D504-10B	10-1/8" (257 mm)	2-1/8" (54 mm)	plastic-dipped	yellow	.79 lbs. (0.36 kg)
D504-12B	12-1/2" (318 mm)	2-3/4" (70 mm)	plastic-dipped	yellow	1.2 lbs. (0.54 kg)
<b>Classic Pump Pliers</b>					
D504-7	7-3/8" (187 mm)	1-3/8" (35 mm)	plastic-dipped	yellow	.34 lbs. (0.15 kg)
D504-10	9-7/8" (250 mm)	2-1/8" (54 mm)	plastic-dipped	yellow	.81 lbs. (0.37 kg)
D504-12	12" (305 mm)	2-3/4" (70 mm)	plastic-dipped	yellow	1.4 lbs. (0.64 kg)



See our complete line of Pump Pliers

[www.kleintools.com](http://www.kleintools.com)



© 2013 Klein Tools, Inc.  
Lincolnshire, IL. 60069-1418  
Printed in U.S.A. 96163