



Powering Business Worldwide

pe.eaton.com

D7 Series General Purpose Plug-In Relay

D7PR2A

UPC:782114160459

Dimensions:

- **Height:** .83 IN
- **Length:** 1.54 IN
- **Width:** 1.1 IN

Weight:.05 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Voltage:** 120V
- **Contact Configuration:** DPDT
- **Contact Material:** Silver alloy
- **Contact Rating:** 15A
- **Cover:** Plain
- **Enclosure:** IP40
- **Indicator:** Optional LED
- **Maximum Voltage:** 300V switching
- **Options:** Mechanical flag indicator
- **Resistance:** 4430 Ohms
- **Series:** D7 series
- **Terminals:** Plug-in

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [D7_R2 3D Inventor](#)
- [D7_R2 AutoCAD 2D Footprint](#)
- [D7_R2 3D Model Xchange](#)
- [D7_R2 2D Drawing Xchange](#)



- [D7_R2 AutoCAD 2D Footprint \(mm\)](#)
- [D7_R2 2D PDF](#)
- [Eaton Specification Sheet - D7PR2A](#)

Certifications:

- UL Listed file E65657
- CSA file No. LR217069
- cRUus
- UL Listed file E37317
- CSA file No. LR217017

Product compliance:

- CE Marked
- RoHS Compliant



Powering Business Worldwide

pe.eaton.com

D7 Series General Purpose Plug-In Relay

D7PR2A

UPC:782114160459

Dimensions:

- **Height:** .83 IN
- **Length:** 1.54 IN
- **Width:** 1.1 IN

Weight:.05 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Voltage:** 120V
- **Contact Configuration:** DPDT
- **Contact Material:** Silver alloy
- **Contact Rating:** 15A
- **Cover:** Plain
- **Enclosure:** IP40
- **Indicator:** Optional LED
- **Maximum Voltage:** 300V switching
- **Options:** Mechanical flag indicator
- **Resistance:** 4430 Ohms
- **Series:** D7 series
- **Terminals:** Plug-in

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [D7_R2 3D Inventor](#)
- [D7_R2 AutoCAD 2D Footprint](#)
- [D7_R2 3D Model Xchange](#)
- [D7_R2 2D Drawing Xchange](#)



- [D7_R2 AutoCAD 2D Footprint \(mm\)](#)
- [D7_R2 2D PDF](#)
- [Eaton Specification Sheet - D7PR2A](#)

Certifications:

- UL Listed file E65657
- CSA file No. LR217069
- cRUus
- UL Listed file E37317
- CSA file No. LR217017

Product compliance:

- CE Marked
- RoHS Compliant