



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DG134245FNC21C DG1 480V FR6 N1 200HP 245A CT 250HP 310A VT Eaton Corp

Catalog Number	DG134245FNC21C
Manufacturer	Eaton Corp
Description	Eaton Powerxl DG1 Series Variable Frequency Drive, 380-500V Input 150 KW 200 HP CT 3PH 50/60 HZ 245A Output IP21/Type 1 Enclosure FR6 LCD Display Internal Emc Filter and DC Choke Ethernet, RS-485, Bacnet MS/TP
Weight per unit	286.0 (lbs/each)
Product Category	Ac Drives

Features

display	LCD graphical
Input Voltage	400 V, 380-500 V(-15%, +10%)
keypad	Included

Dimensions and Weight

Depth	45
Height	21
Width	23.6

Descriptions

Description	DG1 480V FR6 N1 200HP 245A CT 250HP 310A VT
extra long description	ETN DG1-34245FN-C21C PowerXL DG1 se
Features	Demand more flexibility. Eaton's PowerXL DG1 general purpose, variable frequency drives are engineered for today's demanding commercial and industrial applications. With an industry leading energy efficiency algorithm, high short-circuit current rating and robust design, the DG1 offers customers increased efficiency, safety and reliability.
Long Description	Eaton PowerXL DG1 series variable frequency drive, 380-500V input 150 kW 200 Hp CT 3PH 50/60 Hz 245A output IP21/type 1 enclosure FR6 LCD display Internal EMC filter and DC choke EtherNet, RS-485, BACnet MS/TP
Product Type	Powerxl DG1 Series Variable Freq Drive

Manufacturer Information

Brand	Eaton
GTIN	00786680199769
Manufacturers Part Number	DG1-34245FN-C21C
UPC	786680199769

Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Variable Frequency Drive



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 1

Weight Per each 286

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

standard cUL Listed,UL Listed,UL 508C,IEC 61508,EN ISO 13849-1,EN
62061,RoHS Compliant,GoST-R,C-Tick Compliant,CE Marked