



TITLE  
24  
ENERGY SAVER

D703P-W

## Convenient, preset dimming control.

Looking for handsome, high-quality dimmers with smooth, extra-convenient operation? Find just what you're looking for in the P&S Harmony™ line.

Harmony Dimmers feature P&S Decorator style — a great match for any décor. You can easily preset your favorite lighting level with the right-side slide control. Then turn lights on and off with the ergonomically designed paddle switch. It's that simple! There's even an LED that lights when the dimmer is off — no fumbling to find the control in the dark.

You'll find even more convenience in P&S Harmony Dimmers: they won't lose their settings if there's a power failure.

Installation's always quick and easy. And with our durable construction, you can count on many years of dependable service. For convenience and value, you can't go wrong with P&S Harmony Dimmers.

Attractive  
P&S  
Decorator  
style

**Pass & Seymour**



**P&S**

## Decorator Paddle Dimmers

**Green LED glows when off** —  
to make dimmer easy to find  
in the dark.

**Sleek, ergonomic P&S  
Decorator style** matches  
other Decorator devices.

**Convenient operation** —  
combines On/Off Decorator  
switch with separate slider  
for dimming control.

**Constant memory** returns lights to  
previous level after a power failure.

**D703P-W**

Cat. No.	Description	Rating
D703P*	Incandescent Single Pole/3-Way	700W
D1103P*	Incandescent Single Pole/3-Way	1100W
DLV703P*	Magnetic Low Voltage Single Pole/3-Way	700VA
DLV1103P*	Magnetic Low Voltage Single Pole/3-Way	1100VA
DFB8P*	120V Two-Wire Fluorescent Single Pole/3-Way	8A
DDH16P*	De-Hummer Fan Speed Control	1.6A

**\* Color Designation**

I Ivory  
LA Light Almond  
W White  
BK Black  
- Brown

All devices are UL Listed and CSA Certified.

D703P, D1103P and DDH16P are available in VisionPak™.  
Add [V] after the color code.

DFB8P for use with Advance MK10 dimming ballasts.

For additional technical or application-specific information, call  
800-223-4185 or visit our website at [www.passandseymour.com](http://www.passandseymour.com).  
We're eager to put our expertise to work for you.

**Distributed by:**

**USA**  
P.O. Box 4822  
Syracuse, NY 13221-4822  
800-611-7277

**Canada**  
570 Applewood Crescent  
Vaughan, ON, L4K 4B4  
905-738-9195

# Pass & Seymour

[www.passandseymour.com](http://www.passandseymour.com)

SS1501 1/07  
©2007, Pass & Seymour/Legrand AGI/DG

**legrand**



TITLE  
24  
ENERGY SAVER

D703P-W

## Convenient, preset dimming control.

Looking for handsome, high-quality dimmers with smooth, extra-convenient operation? Find just what you're looking for in the P&S Harmony™ line.

Harmony Dimmers feature P&S Decorator style — a great match for any décor. You can easily preset your favorite lighting level with the right-side slide control. Then turn lights on and off with the ergonomically designed paddle switch. It's that simple! There's even an LED that lights when the dimmer is off — no fumbling to find the control in the dark.

You'll find even more convenience in P&S Harmony Dimmers: they won't lose their settings if there's a power failure.

Installation's always quick and easy. And with our durable construction, you can count on many years of dependable service. For convenience and value, you can't go wrong with P&S Harmony Dimmers.

Attractive  
P&S  
Decorator  
style

**Pass & Seymour**



**P&S**


## Decorator Paddle Dimmers

**Green LED glows when off** — to make dimmer easy to find in the dark.

**Sleek, ergonomic P&S Decorator style** matches other Decorator devices.

**Convenient operation** — combines On/Off Decorator switch with separate slider for dimming control.

**Constant memory** returns lights to previous level after a power failure.

**D703P-W**

Cat. No.	Description	Rating
D703P*	Incandescent Single Pole/3-Way	700W
D1103P*	Incandescent Single Pole/3-Way	1100W
DLV703P*	Magnetic Low Voltage Single Pole/3-Way	700VA
DLV1103P*	Magnetic Low Voltage Single Pole/3-Way	1100VA
DFB8P*	120V Two-Wire Fluorescent Single Pole/3-Way	8A
DDH16P*	De-Hummer Fan Speed Control	1.6A

**\* Color Designation**

I Ivory  
**LA** Light Almond  
**W** White  
**BK** Black  
 - Brown

All devices are UL Listed and CSA Certified.

D703P, D1103P and DDH16P are available in VisionPak™. Add [V] after the color code.

DFB8P for use with Advance MK10 dimming ballasts.

For additional technical or application-specific information, call 800-223-4185 or visit our website at [www.passandseymour.com](http://www.passandseymour.com). We're eager to put our expertise to work for you.

**Distributed by:**

**USA**  
 P.O. Box 4822  
 Syracuse, NY 13221-4822  
 800-611-7277

**Canada**  
 570 Applewood Crescent  
 Vaughan, ON, L4K 4B4  
 905-738-9195

# Pass & Seymour

[www.passandseymour.com](http://www.passandseymour.com)

SS1501 1/07  
 ©2007, Pass & Seymour/Legrand AGI/DG

**legrand**