



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH222FRK 60A/2P HD Fusible Safety Switch 240V Nema 3R

Eaton Corp

Catalog Number	DH222FRK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, Enhanced Visible Blade, 60 A, Nema 3R, Class H, Two-Pole, Two-Wire, 240 V, Max HP: 3, 7.5 HP/10, 15 HP/10 HP (1, 3PH @ STD Fuse/Time Delay/250 VDC), #14-#2 Cu/Al
Weight per unit	19.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

Features

amperage rating	60
Material	Galvanized Steel
media	Yes
Poles	2
Voltage Rating	240V

Dimensions and Weight

Depth	16.5
Height	8.5
Width	9.5

Descriptions

Description	60A/2P HD FUSIBLE SAFETY SWITCH 240V NEMA 3R
extra long description	ETN DH222FRK 60A/2P HD Fusible Sfty
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, Enhanced visible blade, 60 A, NEMA 3R, Class H, Two-pole, Two-wire, 240 V, Max Hp: 3, 7.5 hp/10, 15 hp/10 hp (1,3PH @ Std fuse/time delay/250 Vdc), #14-#2 Cu/Al
Product Type	60A/2P HD Fusible Sfty SW 240V N3R
Special Features	Enhanced visible blade

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685176758
Manufacturers Part Number	DH222FRK
UPC	786685176758



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description DISCONNECTS

Type Fusible safety switch

Packaging

Carton 1

Weight Per each 19

Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Power
Distribution and Controls

nema rating 3R

standard UL Listed