



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DG132088FNC21C DG1 230V FR4 N1 30HP 88A CT 40HP 114A VT

Eaton Corp

Catalog Number	DG132088FNC21C
Manufacturer	Eaton Corp
Description	Eaton Powerxl DG1 Variable Frequency Drive, 208-240V Input 22 KW 30 HP CT 3PH 50/60 HZ 88A Output IP21/Type 1 Enclosure FR4 LCD Internal Emc Filter and DC Choke Ethernet, RS-485, Bacnet MS/TP, Modbus TCP and Rtu Ports 2 Exp Slots
Weight per unit	80.0 (lbs/each)
Product Category	Ac Drives

Features

display	LCD graphical
Input Voltage	230 V, 208-240 V(-15%, +10%)
keypad	Included

Dimensions and Weight

Depth	28
Height	16.5
Width	15

Descriptions

Description	DG1 230V FR4 N1 30HP 88A CT 40HP 114A VT
extra long description	ETN DG1-32088FN-C21C DG1,230V FR4,N
Features	Demand more flexibility. Eaton's PowerXL DG1 general purpose, variable frequency drives are engineered for today's demanding commercial and industrial applications. With an industry leading energy efficiency algorithm, high short-circuit current rating and robust design, the DG1 offers customers increased efficiency, safety and reliability.
Long Description	Eaton PowerXL DG1 variable frequency drive, 208-240V input 22 kW 30 Hp CT 3PH 50/60 Hz 88A output IP21/type 1 enclosure FR4 LCD Internal EMC filter and DC choke EtherNet, RS-485, BACnet MS/TP, Modbus TCP and RTU ports 2 exp slots
Product Type	DG1, 230V FR4, N1, 30HP, 88A CT, 40HP, 114A VT
Special Features	Coated board

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685886121
Manufacturers Part Number	DG1-32088FN-C21C
UPC	786685886121



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Variable Frequency Drive

Packaging

Carton	1
Weight Per each	80

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Enclosure standard	IP21/type 1 enclosure EN ISO 13849-1,cUL Listed,EN 62061,UL 508C,IEC 61508,UL Listed,RoHS Compliant,C-Tick Compliant,GoST-R,CE Marked