



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DT364URK 200A/3P HD NF Double Throw Switch 600V Nema 3R

Eaton Corp

Catalog Number	DT364URK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Double-Throw Non-Fused Safety Switch, 200 A, Nema 3R, Painted Galvanized Steel, Non-Fusible, Three-Pole, Three-Wire, 600 Vac, 250 VDC
Weight per unit	80.0 (lbs/each)
Product Category	Non-Fusible Double Throw Safet

Features

amperage rating	200
Material	Galvanized Steel
media	Yes
Poles	3
Voltage Rating	600 VAC, 250 VDC

Dimensions and Weight

Depth	11.26
Height	37.69
Width	19.15

Descriptions

Description	200A/3P HD NF DOUBLE THROW SWITCH 600V NEMA 3R
extra long description	ETN DT364URK 200A/3P HD NF DT Sw 60
Features	Eaton's double-throw safety switches include two interlocked switches with a common connection used to transfer service from a normal power source to an alternate source, or to switch from one load circuit to another. The interlock ensures both switches cannot be closed at the same time, preventing them from being operated in parallel. Additionally, double-throw safety switches are available in general duty and heavy duty as well as quick-connect options.
Long Description	Eaton Heavy duty double-throw non-fused safety switch, 200 A, NEMA 3R, Painted galvanized steel, Non-fusible, Three-pole, Three-wire, 600 Vac, 250 Vdc
Product Type	200A/3P HD NF DT SW 600V N3R



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113613987
Manufacturers Part Number	DT364URK
UPC	782113613987

Taxonomies, Classifications, and Categories

Category Description	DOUBLE THROW SWITCHES (DT Series)
Type	Double-throw non-fused safety switch

Packaging

Carton	1
Weight Per each	80

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
standard	UL Listed