



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DVSTVBL Diva DV 8A 0-10V 3WAY Black

Lutron

|                  |  |
|------------------|--|
| Catalog Number   | DVSTVBL  |
| Manufacturer     | Lutron   |
| Description      | Diva Dimmer - Gloss Finish, Fluorescent or Led Dimming With 0-10V Ballasts and Drivers, Single-Pole/3-Way, 120-277V/50MA/8A In Black |
| Weight per unit  | 0.2600 (lbs/each)  |
| Product Category | Lighting Dimmers   |

### Features

|                 |               |
|-----------------|---------------|
| actuator        | Paddle Switch |
| amperage rating | 8             |
| connection      | Wire Leads    |
| Connection Type | Wire Leads    |
| insulation      | Plastic       |
| Material        | Plastic/Metal |
| media           | Yes           |
| Poles           | 1             |
| Switch Type     | Paddle Switch |
| Voltage Rating  | 120 to 277    |
| Wattage         | 2216          |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Color  | Black |
| Finish | Gloss |

### Dimensions and Weight

|      |                      |
|------|----------------------|
| Size | 4.69 x 2.94;119 x 75 |
|------|----------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | DIVA DV 8A 0-10V 3WAY BLACK   |
| extra long description | LUT DVSTV-BL DIVA 0-10 W/SWITCHING  |
| Features               | The Diva 0-10V dimmer switch is a simple solution is designed to match existing design style switches and accessories. Easily turn the lights on and off with a paddle switch, and use the slide control to adjust the lights to the perfect level. The new Diva 0 - 10-Volt dimmerswitch is a 0-10 VDC dimmer with 3-way functionality for 3rd party 0-10-Volt fixtures (LED and fluorescent), no separate power pack required. Coordinating wall plate sold separately. |
| Long Description       | Diva Dimmer - Gloss Finish, Fluorescent or LED Dimming with 0-10V Ballasts and Drivers, Single-pole/3-way, 120-277V/50mA/8A in black  |
| Product Type           | Diva 0-10 W/Switching Box Black   |
| Special Features       | Controls 0-10 V LED or fluorescent fixture loads, 50 mA max control current. Paddle turns on/off. Slide up to brighten, down to dim.  |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Lutron         |
| GTIN                      | 00784276099578 |
| Manufacturers Part Number | DVSTV-BL       |
| UPC                       | 784276099578   |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
| Type                 | Dimmer, 3-way/single-pole                                    |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 24   |
| Weight Per each | 0.26 |

## Uses, Certifications, and Standards

|                          |                  |
|--------------------------|------------------|
| Application              | Lighting Control |
| Enclosure                | Plastic          |
| environmental conditions | Indoor use only  |
| Mounting                 | WALLBOX          |
| Operating Temperature    | 32 to 104        |
| standard                 | UL, CSA          |