



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E22JPLB2 PSHPLL JMASHD BKBZ R

Eaton Corp

Catalog Number	E22JPLB2
Manufacturer	Eaton Corp
Description	Eaton E22 Pushbutton, E22 Pushbutton, 22.5 MM, Non-Metallic Heavy-Duty, 50 MM, Nema 3, 3R, 4, 4X, 12, 13, Non-Illuminated, Maintained Contact, Push-to-Latch, Pull to Release, Red Actuator, Mushroom , Plastic, No Light Unit, Black Bezel
Weight per unit	0.0200 (lbs/each)
Product Category	Push Button Components

Features

actuator	Jumbo mushroom
dimensions	4.5000 IN X 4.0000 IN X 2.0000 IN

Dimensions and Weight

Size	50 mm
------	-------

Descriptions

Description	PSHPLL JMASHD BKBZ R
extra long description	ETN E22JPLB2 PSHPLL JMASHD BKBZ R
Features	Eaton's 22.5 mm industrial heavy-duty pushbutton line offers a wide array of functional, smartly styled illuminated and non-illuminated pushbuttons, selector switches, push-pulls, action and twist-to- release operators. The complete line also includes transformer, full voltage, resistor, LED or neon light units.
Long Description	Eaton E22 pushbutton, E22 Pushbutton, 22.5 mm, Non-Metallic Heavy-Duty, 50 mm, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Maintained contact, push-to-latch, pull to release, Red actuator, Mushroom , Plastic, No light unit, Black bezel
Product Type	PSHPLL JMASHD BKBZ R

Manufacturer Information

Brand	Eaton
GTIN	00782113573502
Manufacturers Part Number	E22JPLB2
UPC	782113573502

Taxonomies, Classifications, and Categories

Category Description	MINATURE PILOT DEVICES.22MM
Type	PUSHBUTTON

Packaging

Carton	1
Weight Per each	0.02



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Stationary Machinery and Equipment Outside Factory -

Stationary Machinery and Equipment Outside Factory - Other

standard

CSA Certified, Lloyd's Register Certified, UL 508, IEC 947-5-1

MTTA, CE Marked