



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## E50KL40 E50 Operating Lever

Eaton Corp

Catalog Number	E50KL40
Manufacturer	Eaton Corp
Description	E50 Nema Limit Switch, Lever, Rotary Lever, 1.38 Inch Len, Stainless Steel, Metal Roller 0.75 Inch Diameter 0.32 Inch Width, 14-250F(-10-121C), Stainless Steel, Steel, Ul, Csa, Ce
Weight per unit	0.1000 (lbs/each)
Product Category	Limit Switch Arms, Actuators &

### Features

actuator	Standard roller
dimensions	2.1000 IN X 0.7500 IN X 0.6500 IN

### Descriptions

Description	E50 OPERATING LEVER
extra long description	ETN E50KL40 E50 LS LEVER,SS,MET ROL
Features	Eaton's E50 modular plug-in limit switches are the industry standard with versatility of design and high reliability for low maintenance, installation and inventory costs. Standard Viton gaskets, seals and boots and a zinc die -cast enclosure provide exceptional chemical resistance to the common coolants, cleansing agents and hydraulic fluids found in machine tool, automotive, wastewater treatment and other heavy-duty industrial applications. Mounting dimensions accommodate both U.S. and DIN standards for
Long Description	E50 NEMA Limit Switch,Lever,Rotary lever,1.38 inch len,Stainless steel,Metal roller 0.75 inch diameter 0.32 inch width,14-250F(-10-121C),Stainless Steel,Steel, UL,CSA,CE
Product Type	E50 LS Lever, SS, Met Roller, 1.38IN Length

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113317496
Manufacturers Part Number	E50KL40
UPC	782113317496

### Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
Type	Heavy duty plug-in limit switch accessory

### Packaging

Carton	1
Weight Per each	0.1



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application .....	Ind Facilities & Factories - Industrial Facilities/Factories - Other .....
standard .....	CSA Certified,UL Listed,CE,RoHS Compliant,CE Marked .....