



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E50KL539 E50 Operating Lever

Eaton Corp

Catalog Number	E50KL539
Manufacturer	Eaton Corp
Description	E50 Nema Limit Switch, Lever, Rotary Lever, Adj, 3.75 Inch Len, Type 303 Stainless Steel Lever, Ball Bearing Roller 0.75 Inch Diameter 0.32 Inch Width, 14-250F(-10-121C), Stainless Steel, Steel, Ul, Csa, Ce
Weight per unit	0.1500 (lbs/each)
Product Category	Limit Switch Arms, Actuators &

Features

actuator	Adjustable ball bearing roller
dimensions	4.6000 IN X 0.6900 IN X 0.8400 IN

Descriptions

Description	E50 OPERATING LEVER
extra long description	ETN E50KL539 E50 LS LEVER,SS,BB ROL
Features	Eaton's E50 modular plug-in limit switches are the industry standard with versatility of design and high reliability for low maintenance, installation and inventory costs. Standard Viton gaskets, seals and boots and a zinc die -cast enclosure provide exceptional chemical resistance to the common coolants, cleansing agents and hydraulic fluids found in machine tool, automotive, wastewater treatment and other heavy-duty industrial applications. Mounting dimensions accommodate both U.S. and DIN standards for
Long Description	E50 NEMA Limit Switch,Lever,Rotary lever,adj,3.75 inch len,Type 303 Stainless steel lever,Ball Bearing roller 0.75 inch diameter 0.32 inch width,14-250F(-10-121C),Stainless Steel,Steel,UL,CSA,CE
Product Type	E50 LS Lever, SS, BB Roller, 3.75IN Adj

Manufacturer Information

Brand	Eaton
GTIN	00782113361871
Manufacturers Part Number	E50KL539
UPC	782113361871

Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
Type	Heavy duty plug-in limit switch accessory



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.15

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	CE,CSA Certified,UL Listed,RoHS Compliant,CE Marked