



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E5718LE20AB 18MM Ext Range Ind Prox 2W Ac Mini *Eaton Corp*

Catalog Number	E5718LE20AB
Manufacturer	Eaton Corp
Description	E57 Two-Wire Series Tubular Inductive Proximity Sensor Enclosure, 0.71 Dia, Dist. 20 MM, 2-Wire Ac, No, 300 Ma At 132 Vac, 3 Pin Mini Connector, 20-132 Vac Input, <3% Of Sensing Distance Accuracy, None, Non-Embeddable
Weight per unit	0.2500 (lbs/each)
Product Category	Inductive Proximity Sensor

Features

dimensions	0.7100 IN X 0.7100 IN X 3.3900 IN
media	Yes

Descriptions

Description	18MM EXT RANGE IND PROX 2W AC MINI
extra long description	ETN E57-18LE20-AB 18MM EXT RANGE IN
Features	E57G general purpose sensors are a cost-effective solution that is optimised to include only those functions that are necessary for basic, reliable sensing without lacking the performance or features you expect in an Eaton product. These sensors include various diameter options designed to fit a variety of applications.
Long Description	E57 Two-Wire Series Tubular Inductive Proximity Sensor Enclosure, 0.71 dia, dist. 20 mm, 2-Wire AC, NO, 300 mA at 132 Vac, 3 Pin Mini Connector, 20-132 Vac input, <3% of sensing distance accuracy, None, Non-embeddable
Product Type	18MM Ext Range Ind Prox 2W Ac Mini

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113933450
Manufacturers Part Number	E5718LE20AB
UPC	782113933450

Taxonomies, Classifications, and Categories

Category Description	SENSORS
Type	Inductive Proximity Sensor

Packaging

Carton	1
Weight Per each	0.25



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Stationary Mach Equip In Factory - Other Stationary Machinery
and Equipment - In Factory

standard

CSA Certified,UL Listed,CE Marked